


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		AA	REVISED PER ECO-14-015277	18FEB2015	NK	DR

D


C

B

A



STYLE A



STYLE B
INSULATION RESTRICTING

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- STAMP "AMP - SEE TABLE" APPROX AS SHOWN.
- WIRE INSULATION DIA: SEE TABLE.
- TONGUE MATERIAL THK: .039±.002.
- BODY: TIN PLATE .000100 MIN EXT THK PER ASTM B545.
- SLEEVE: TIN PLATE .000100 MIN EXT THK PER ASTM B545.
- SLEEVE: NICKEL PLATE PER QQ-N-290.
- BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
COLOR - YELLOW.
- APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- MEETS MS25036-112, CLASS 1 & 2.
- MEETS MS25036-112, CLASS 2.
- MEETS M7928/1-58, CLASS 1 & 2.
- MEETS M7928/1-65, CLASS 1 & 2.
- MEETS M7928/1-56, CLASS 1 & 2.
- MEETS M7928/1-63, CLASS 1 & 2.
- NOTE DELETED.

D

C

B

A

50	LOOSE PIECE, BOX	#10	.197	12-10	.150-.230	12-10	--	A	4	5	8-36161-2	
2500	ON TAPE & REEL	#10	.197	12	.119-.200	12	BROWN	B		6	12	2-36161-8
---	LOOSE PIECE	#6	.145	10	.119-.200	10	BROWN	B		6	14	2-36161-6
---	LOOSE PIECE	#6	.145	12	.095-.200	12	YELLOW	B		6	13	2-36161-5
---	LOOSE PIECE	#10	.197	10	.119-.200	10	BROWN	B		6	12	2-36161-4
---	LOOSE PIECE	#10	.197	12	.095-.200	12	YELLOW	B		6	11	2-36161-3
2500	ON TAPE & REEL	#10	.197	12-10	.150-.230	12-10	--	A		5	10	2-36161-2
---	LOOSE PIECE	#10	.197	12-10	.150-.230	12-10	--	A		5	9	36161
QTY	PACKAGE TYPE	"H"	"C"	STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY FINISH	SLEEVE FINISH	PART NO	

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 17DEC09		 TE Connectivity										
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX		DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, RING TONGUE, PIDG WIRE SIZE: 12-10 AWG									
				CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED OR SOLID				0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -											
FOR APPLICATION		TOOLING ASSISTANCE CENTER		MATERIAL		FINISH		APVD T MICHELUTTI 17DEC09		PRODUCT SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
TOOLING INFORMATION		1-800-722-1111						APPLICATION SPEC		—		WEIGHT		A2		00779	C=36161	—	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		—		—		CUSTOMER DRAWING				SCALE	5:1	SHEET	1 of 1	REV	AA