



Actual

Catalog Number: L-24-120-9-L
Product ID: 7TAG054410R0012
UPC Number: 72849491274
EAN Number: 05414363128366
Status: Active

Heavy Duty Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 599.72mm (23.611 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.91mm (0.075 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

- Application Tools: ERG120

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Heavy-Duty
Standard	UL E49405
Width	0.30 Inch/7.62mm
Length	23.611 Inches/599.72mm
Thickness	0.075 Inch/1.91mm
Bundle Diameter	0.187 Inches-4.76mm-7.0 Inches/177.8mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	120 Pounds/534 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7.62mm
Length belt/tape/tie	599.72mm
Tie thickness	1.91mm
Min. holding force	534N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	50
Inner Dimensions (inches)	27.1x4.8x2.05
Outer Quantity	500
Outer Dimensions (inches)	30x7.8x8.3
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com