



Actual

Catalog Number: A18-PS-M
Product ID: 7TAI029620R0001
UPC Number: 78621093625
EAN Number: 05414363935339
Status: Active

Non-Insulated Parallel Splice, Length .314 Inches, Outer Diameter .129 Inches, Inner Diameter .086 Inches, Wire Range #22-#16 AWG 509kcmi-3,260kcmil, Copper, Tin Plated

- Resistant to corrosion and preserve the electrical integrity of the wires in single or multiple strands.
- Feature an intelligent constructable part number for quick identification of the wire range.
- Application Tools: ERG4002, WT111M, WT112M, WT2000

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Special Features	Resistant to corrosion and preserve the electrical integrity of the wires in single or multiple strands. Feature an intelligent constructable part number for quick identification of the wire range.
Standard	UL E9809
Material	Copper
Finish	Tin Plated
Color	Metallic
Voltage Rating	600V

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	22-16
Material	Copper
Surface protection	Tinned
Insulation	None

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	10000
Outer Dimensions (inches)	12.25x6x3.5
Weight Uom	0.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000229

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com