








Model Number

NMB15-30GM65-E0-V1

Features

- 15 mm flush
- Stainless steel sensing face
- Increased operating distance

Connection



Pinout



Wire colors in accordance with EN 60947-5-2

1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Accessories

V1-G-2M-PUR

2012-12-13 911277_eng.xml

Date of issue:


Release date: 2012-12-13 14:34

Cable socket, M12, 4-pin, PUR cable

V1-W-2M-PUR Cable socket, M12, 4-pin, PUR cable

Mounting aid

Dimensions



Technical Data

General	specification	15
---------	---------------	----

Switching element function		NPN NO
Rated operating distance	Sn	15 mm
Installation		flush (Requirements: see drawing below)
Output polarity		DC
Assured operating distance	Sa	0 12.15 mm
Actuating element		Ferrous and nonferrous targets
Reduction factor r _{Al}		0.4
Reduction factor r _{Cu}		0.2
Reduction factor r ₃₀₄		0.85
Reduction factor r _{St37}		1
Nominal ratings		
Operating voltage	U _B	10 30 V DC
Switching frequency	f	0 150 Hz
Hysteresis	Н	3 15 typ. 10 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U _d	≤2 V
Operating current	IL.	≤ 200 mA
Off-state current	l _r	≤ 10 μA
No-load supply current	I ₀	≤ 10 mA
Operating voltage display		LED, green
Indication of the switching state		LED, yellow
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)

Mechanical specifications

Device connector M12 x 1 , 4-pin Stainless steel 1.4305 / AISI 303 Stainless steel 1.4305 / AISI 303 Connection type Housing material

Sensing face


Protection degree IP67 / IP68 / IP69K - cordset dependent according to cable speci-

Compliance with standards and directives Standard conformity

Standards EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval cULus Listed, General Purpose CSA approval cCSAus Listed, General Purpose Products with a maximum operating voltage of ≤36 V do not bear a CCC marking because they do not require approval. CCC approval



Sensor face is flush with mounting surface.