









Model number


VBG-ENX-K20-DMD

EtherNet/IP + Modbus TCP Gateway, double master for 2 AS-Interface networks


Features

- Gateway compliant with AS-Interface specification 3.0
- Connection to Ethernet Modbus TCP/IP
- · 2 AS-Interface networks
- · Dublicate addressing detection
- Integrated webserver
- Earth fault detection
- AS-Interface noise detection
- Ethernet diagnostic interface
- Integrated switch allows line topology
- DLR technology supports ring topology

Dimensions




Electrical connection



AS-Interface circuit 1 and 2 are supplied from different power supplies. At the cable for power supply no slaves or repeaters may be attached. At the cable for AS-Interface circuit no power supplies or further masters may be attached.

Indicating / Operating means



Technical data General specifications V3.0 AS-Interface specification **PLC-Functionality** activateable Duplicate address detection from AS-Interface slaves Earth fault detection integrated **EMC** monitoring integrated Diagnostics function Extended function via display **UL File Number** E223772 Functional safety related parameters $MTTF_d$ 100 a at 30 °C Indicators/operating means Display Illuminated graphical LC display for addressing and error mes-LED ETHERNET ethernet active; LED green LED AS-i ACTIVE AS-Interface operation normal; LED green LED CONFIG ERR configuration error; LED red LED PRG ENABLE autom. programming; LED green LED POWER voltage ON; LED green LED PRJ MODE projecting mode active; LED yellow LEDUAS-i AS-Interface voltage; LED green Button **Electrical specifications** > 500 V Insulation voltage Ui U_e Rated operating voltage from AS-Interface 30 V DC Rated operating current ≤ 200 mA from AS-Interface circuit 1 I_{e} ≤ 70 mA from AS-Interface circuit 2 Interface 1 Interface type Protocol EtherNet/IP + MODBUS TCP/IP according to IEEE 802.3 supports device level ring protocol DLR Transfer rate 10 MBit/s / 100 MBit/s , Automatic baud rate detection Interface 2 Interface type RS 232, serial

Connection	
Ethernet	RJ-45
AS-Interface	spring terminals, removable
Ambient conditions	
Ambient temperature	0 55 °C (32 131 °F)

Storage temperature

Transfer rate

Interface type

Interface 3

Mechanical specifications Degree of protection IP20 Mass 500 g Construction type Low profile housing, Stainless steel

-25 ... 85 °C (-13 ... 185 °F)

Diagnostic Interface

19,2 kBit/s

Chip card slot

C V

Compliance with standards and directi- ies	
Directive conformity	
EMC Directive 2004/108/EC	EN 61000-6-2:2005, EN 61000-6-4:2007
Standard conformity	
Electromagnetic compatibility	EN 61000-6-2:2005, EN 61000-6-4:2007
AS-Interface	EN 50295:1999
Degree of protection	EN 60529:2000
Shock and impact resistance	EN 61131-2:2004
Standards	EN 61000-6-2:2005, EN 61000-6-4:2007 EN 954-1:1996 (up to Kategorie 4), IEC 61508:2001 and EN 62061:2005 (up to SIL3) EN 13849:2008 (PL e)

Notes

In an AS-Interface network only one device can be operated earth fault detection. If there are many devices in an AS-Interface network, this can lead to the earth fault monitoring response threshold becoming less sensitive.

Function

The VBG-ENX-K20-DMD is an Ethernet/IP + Modbus TCP gateway with 2 AS-Interface masters in accordance with AS-Interface specification 3.0. This means that data can be transferred from 2 parallel AS-Interface branches via one IP address.

The design of the K20 in stainless steel with IP20 is particularly suited for use in switching cabinets for snap on mounting on the 35 mm mounting rail.

The gateway in accordance with the AS-Interface specification V 3.0 is used to connect AS-Interface systems to a higher-level net. It acts as a master for the AS-Interface segment and as a slave for the higher-level net. During cyclic data exchange, the digital data of an AS-Interface segment is transferred. Analog values as well as the complete command set of the new AS-Interface specification are transferred using a command interface.

The address allocation and acceptance of the target configuration can be achieved via the keys. 7 LEDs fitted to the front panel indicate the actual state of the AS-Interface branch.

With the graphical display, the commissioning of the AS-Interface circuits and testing of the connected peripherals can take place completely separately from the commissioning of the higher-level network and the programming. With the 4 switches, all functions can be controlled and visualized on the display.

The device has a card slot for a memory card for the storage of configuration data.

An integrated Switch and 2 RJ-45 sockets allow the design of a line topology without the use of an external Switch.

The device level ring protocol DLR increases the reliability of a ring topology at the device level, thus optimizing the machine running times.

An integrated webserver allows to administrate the device and The AS-interface network without additional hard and/or software via a browser interface.

The redundant power supply guarantees that the double master remains in function and is diagnosticable, when a failure of a power supply unit in one of the two AS-interfaces circles occures. Also communication with the superior field bus is not disturbed by the failure of a power supply.

PLC Functionality

Optionally the gateway is also available with PLC functionality. Therefor you can order a E code key VAZ-CTR additionally.

Accessories

VAZ-SW-ACT32

Full version of the AS-I Control Tools including connection cable

PEPPERL+FUCHS

USB-0.8M-PVC ABG-SUBD9

Interface converter USB/RS 232

eng.) 2014-03-18 Date of issue: Release date: 2014-03-18 17:27