



Actual

**Catalog Number:** L-14-120-9-C  
**Product ID:** 7TAG054410R0006  
**UPC Number:** 72849491170  
**EAN Number:** 05414363128304  
**Status:** Active

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 362.81mm (14.284 Inches), Width of 7.62mm (0.30 Inches), Thickness of 1.91mm (0.075 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

- Application Tools: ERG120

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Heavy-Duty
Standard	UL E49405
Width	0.30 Inch/7.62mm
Length	14.284 Inches/362.81mm
Thickness	0.075 Inch/1.91mm
Bundle Diameter	0.187 Inches/4.76mm-4.0 Inches/101.6mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	120 Pounds/534 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	7.62mm
Length belt/tape/tie	362.81mm
Tie thickness	1.91mm
Min. holding force	534N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

### Packaging

Inner Quantity	100
Inner Dimensions (inches)	20x6x3
Outer Quantity	3000
Outer Dimensions (inches)	18.1x12.8x13.6
Weight Uom	0.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000223

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)