



Actual



Representative

**Catalog Number:** 2920AL  
**Product ID:** 7TBD105090R0000  
**UPC Number:** 78621079713  
**EAN Number:** 05414363140320  
**Status:** Active

Liquidtight Strain Relief Connector, 1/2 Inch, Straight, Cord Range 0.125 to 0.375 Inch, Throat Diameter 9/16 Inch, Aluminum Body, Glandnut, and Grip, Rubber Bushing

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.
- Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	A Liquidtight Fitting to Secure Flexible Cord or Power Cable to a Box or Enclosure and Provide Strain Relief
Standard	UL E13938, CSA 52391
Size	1/2 Inch
Conductor Range	0.125 to 0.375 Inch
Material	Aluminum
Color	Metallic
Environmental Conditions	Ordinary, Wet, or Dry Locations

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Thread length	15.875mm
Suitable for cable diameter	3.175-9.525mm
Material	Metal
Material quality	Aluminium
Colour	Natural colour
Model	Straight
Strain relief	Y

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	6x4.5x4
Outer Quantity	100
Outer Dimensions (inches)	13x9.9x4.2
Weight Uom	8 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA  
Technical Data Sheet Global

Available on Website  
wsd-000077

---

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)