



Representative

**Catalog Number:** J20-38  
**Product ID:** 7TAI029580R0038  
**UPC Number:** 78621080370  
**EAN Number:** 05414363153184  
**Status:** Active

Non-Insulated Tubular Ring Terminal, Length 1.84 Inches, Width .83 Inches, Bolt Hole 3/8 Inch, Wire Range 1/0AN-2/0, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: TBM6, TBM6S, WT3185

### North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	2/0
Voltage Rating	600V
Material	Copper
Color	Metallic

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Flange shape	Ring shape
Slender flange model	N
Insulated	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	2.5x1.3x3.5
Outer Quantity	100
Outer Dimensions (inches)	7.4x5.6x3.7
Weight Uom	6.38 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)