









# **Model Number**

SJ3,5-N

## **Features**

- 3.5 mm slot width
- Usable up to SIL2 acc. to IEC 61508

Depth of immersion (lateral) 5 ... 7 mm , typ. 6 mm

Installation
Output polarity NAMUR Nominal ratings

 $8.2~V~(R_i~approx.~1~k\Omega)$  5~...~25~V~ 0~...~3000~HzNominal voltage Operating voltage Switching frequency Hysteresis

0.41 ... 0.6 mm
yes , Reverse polarity protection diode not required Suitable for 2:1 technology

Current consumption

Measuring plate not detected  $\leq$  1 mA

Measuring plate detected
Functional safety related parameters

MTTF<sub>d</sub> Mission Time (T<sub>M</sub>) 8415 a 20 a Diagnostic Coverage (DC) 0 %

**Ambient conditions** 

Ambient temperature -25 ... 100 °C (-13 ... 212 °F)

Mechanical specifications

Connection type flexible leads LiY, 500 mm

Core cross-section PBT/PPS Housing material Degree of protection IP67

General information

see instruction manuals 1G; 2G; 1D Use in the hazardous area

Category

Compliance with standards and directives

Standard conformity NAMUR EN 60947-5-6:2000 IEC 60947-5-6:1999

EN 60947-5-2:2007 Standards IEC 60947-5-2:2007

Approvals and certificates


FM approval

Control drawing 116-0165


**UL** approval cULus Listed, General Purpose CSA approval cCSAus Listed, General Purpose

CCC approval CCC approval / marking not required for products rated ≤36 V

# **Dimensions**



# **Electrical Connection**



### ATEX 1G

Instruction

Device category 1G

**EC-Type Examination Certificate** 

CE marking

ATEX marking

Directive conformity

Standards

Appropriate type

Effective internal capacitance Ci Effective internal inductance Li

General

Ambient temperature

Installation, commissioning

Maintenance

## Special conditions

Protection from mechanical danger

## Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist

PTB 99 ATEX 2219 X **(€**0102

⟨Ex⟩ II 1G Ex ia IIC T6...T1 Ga

94/9/EG

EN 60079-0:2012, EN 60079-11:2012, EN 60079-26:2007 Ignition protection "Intrinsic safety"

Use is restricted to the following stated conditions

≤ 50 nF; a cable length of 10 m is considered.

 $\leq$  250  $\mu H$ ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate. Note: Use the temperature table for category 1 !!! The 20 %reduction in accordance with EN 1127-1:2007 has already been accounted for in the temperature table for category 1.

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

The associated apparatus must satisfy the requirements of category ia. Due to the possible danger of ignition, which can arise due to faults and/or transient currents in the equipotential bonding system, galvanic isolation of the power supply and signal circuit is preferable. Associated apparatus without electrical isolation must only be used if the appropriate requirements of IEC 60079-14 are met.

Install the device in such a way that the resin surface is not exposed to mechanical

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20  $^{\circ}\text{C}$  the sensor should be protected from knocks by the provision of an additional housing.



### ATEX 2G

Instruction

## Device category 2G

EC-Type Examination Certificate

CE marking

ATEX marking Directive conformity

Standards

Appropriate type

Effective internal capacitance Ci Effective internal inductance Li

General

Ambient temperature

Installation, commissioning

Maintenance

#### Special conditions

Protection from mechanical danger

## Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist PTB 99 ATEX 2219 X €0102

⟨ II 1G Ex ia IIC T6...T1 Ga

94/9/EG

EN 60079-0:2012, EN 60079-11:2012

Ignition protection "Intrinsic safety"
Use is restricted to the following stated conditions

SJ3,5-...-N...

 $\leq$  50 nF; a cable length of 10 m is considered.

 $\leq$  250  $\mu$ H; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety. Install the device in such a way that the resin surface is not exposed to mechanical hazards.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20 °C the sensor should be protected from knocks by the provision of an additional housing.

### ATEX 1D

Instruction

### Device category 1D

EC-Type Examination Certificate CE marking

ATEX marking Directive conformity Standards

Appropriate type

Effective internal capacitance C<sub>i</sub> Effective internal inductance L<sub>i</sub>

General

Maximum housing surface temperature

Installation, commissioning

Maintenance

## Special conditions

Electrostatic charge

### Manual electrical apparatus for hazardous areas

for use in hazardous areas with combustible dust ZELM 03 ATEX 0128 X **C €**0102

94/9/EG

IEC 61241-11:2002: draft; prEN61241-0:2002 type of protection intrinsic safety "iD" Use is restricted to the following stated conditions

SJ3,5-...-N...

 $\leq$  50 nF ; a cable length of 10 m is considered.

 $\leq$  250  $\mu$ H; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual.

The EC-Type Examination Certificate has to be observed.

The special conditions must be adhered to!

The maximum surface temperature of the housing is given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

The associated apparatus must satisfy at least the requirements of category ia IIB or iaD. Because of the possibility of the danger of ignition, which can arise due to faults and/or transient currents in the equipotential bonding system, galvanic isolation in the power supply and signal circuits is preferable. Associated apparatus without electrical isolation must only be used if the appropriate requirements of IEC 60079-14 are met

The intrinsically safe circuit has to be protected against influences due to lightning. When used in the isolating wall between Zone 20 and Zone 21 or Zone 21 und Zone 22 the sensor must not be exposed to any mechanical danger and must be sealed in such a way, that the protective function of the isolating wall is not impaired. The applicable directives and standards must be observed.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

The connection cables are to be laid in accordance with EN 50281-1-2 and must not normally be subjected to chaffing during use.