









Model Number

UC2000-30GM-IUR2-V15


Single head system

Features

- Parameterization interface for the application-specific adjustment of the sensor setting via the service program ULTRA 3000
- Analog current and voltage output
- Synchronization options
- Adjustable acoustic power and sensitivity
- **Temperature compensation**

Diagrams

Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

Technical data noral enocifications

aenerai specifications	
Sensing range	80 2000 mm
Adjustment range	120 2000 mm
Dead band	0 80 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 180 kHz
Response delay	65 ms minimum
	195 ms factory setting

ators/operating means

malcators/operating means	
LED green	solid: Power-on flashing: Standby mode or program function object detected
LED yellow 1	solid: object in evaluation range flashing: program function

LED yellow 2 solid: object in detection range flashing: program function LED red solid: temperature/program plug not connected

flashing: fault or program function object not detected Temperature/TEACH-IN connector Temperature compensation, Evaluation range programming , output function setting

Electrical specifications

10 ... 30 V DC , ripple 10 %SS Operating voltage UB

Power consumption P₀ ≤ 900 mW Interface

Interface type RS 232, 9600 Bit/s , no parity, 8 data bits, 1 stop bit

Input/Output

Synchronization bi-directional

0 level -U_B...+1 V 1 level: +4 V...+U_B input impedance: > 12 KOhm

synchronization pulse: ≥ 100 µs, synchronization interpulse period: ≥ 2 ms

Synchronization frequency

Common mode operation ≤ 30 Hz

Multiplex operation \leq 30 Hz / n , n = number of sensors , n \leq 5

Output

Output type	1 current output 4 20 mA	
	1 voltage output 0 10 V	

Switch-on delay ton < 150 ms evaluation range [mm]/4000, but \geq 0.35 mm Resolution

Deviation of the characteristic curve ≤ 0.2 % of full-scale value Repeat accuracy ≤ 0.1 % of full-scale value current output: ≤ 500 Ohm Load impedance Voltage output: ≥ 1000 Ohm

≤2 % from full-scale value (with temperature compensation) Temperature influence

≤ 0.2 %/K (without temperature compensation)

Ambient conditions

-25 ... 70 °C (-13 ... 158 °F) Ambient temperature Storage temperature -40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications Connection type Connector M12 x 1, 5-pin

Degree of protection IP65

Material

Housing stainless steel (1.4305 / AISI 303)

PBT plastic parts Transducer

epoxy resin/hollow glass sphere mixture; polyurethane foam Mass 170 g

Factory settings

evaluation limit A1: 200 mm Output

evaluation limit A2: 2000 mm

rising ramp

Compliance with standards and directives

Standard conformity

Standards EN 60947-5-2:2007+A1:2012 IEC 60947-5-2:2007 + A1:2012

EN 60947-5-7:2003 IEC 60947-5-7:2003


Approvals and certificates

EAC conformity TR CU 020/2011

cULus Listed, General Purpose UL approval CSA approval cCSAus Listed, General Purpose


CCC approval CCC approval / marking not required for products rated ≤36 V

Dimensions




Additional Information

Analogue output function



Electrical Connection

Standard symbol/Connection: (version IU)



Core colors in accordance with EN 60947-5-2.

Pinout



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

Accessories

BF 30

Mounting flange, 30 mm

BF 30-F

Mounting flange with dead stop, 30 mm

BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

UVW90-M30

Ultrasonic -deflector

UVW90-K30

Ultrasonic -deflector

UC-30GM-PROG

ULTRA3000

Software for ultrasonic sensors, comfort line

UC-30GM-R2

DA5-IU-2K-V

Process control and indication equipment

V15-G-2M-PVC

Female cordset, M12, 5-pin, PVC cable

Description of Sensor Functions

Programming procedure

The sensor features 2 programmable analog outputs with programmable evaluation range. Programming the evaluation range and the operating mode is done either via the sensor's RS232 interface and ULTRA3000 software (see the ULTRA3000 software description) or by means of the programming plug at the sensor's back end which is described here.



Coded plug

Programming of Evaluation Range

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Place the target at the desired position for A1
- 5. Momentarily insert the programming plug in position A1 and then remove. This will program the position A1.
- 6. Place the target at the desired position for A2
- 7. Momentarily insert the programming plug in position A2 and then remove. This will program the position A2.

Notes:

- Removing the programming plug saves the new position into the device memory.
- The programming status is indicated by the LED. A flashing green LED indicates that the target is detected; a flashing red LED indicates that
 no target is detected.

Programming the Operation Mode

If the program mode is still activated, continue at number 4. If not, activate program mode by performing the sequence numbers 1 to 3.

- 1. Disconnect supply voltage
- 2. Remove the programming plug to activate program mode.
- 3. Reconnect supply voltage (Reset)
- 4. Insert the programming plug in position E2/E3. By removing and reinserting the plug, the user can toggle through the three different modes of operation. The selected mode is indicated by the LEDs as shown below:
 - Rising slope mode, LED A2 flashes
 - Falling slope mode, LED A1 flashes
 - Zero line mode, LEDs A1 and A2 flash
- 5. Once the desired mode is selected, insert the programming plug in position T. This completes the programming procedure and saves the switch points and mode of operation.
- 6. The sensor now operates in normal mode.

Note:


The programming plug also functions as the temperature compensation. If the programming plug has not been inserted in the T position within 5 minutes, the sensor will return to normal operating mode with the latest saved values, without temperature compensation.

Factory settings

See technical data.

Display

The sensor provides LEDs to indicate various conditions.



Synchronization

This sensor features a synchronization input for suppressing ultrasonic mutual interference ("cross talk"). If this input is not connected, the sensor will operate using internally generated clock pulses. It can be synchronized by applying an external square wave. The pulse duration must be ≥ 100 µs. Each falling edge of the synchronization pulse triggers transmission of a single ultrasonic pulse. If the synchronization signal remains low for ≥ 1 second, the sensor will revert to normal operating mode. Normal operating mode can also be activated by opening the signal connection to the synchronization input (see note below).

If the synchronization input goes to a high level for > 1 second, the sensor will switch to standby mode, indicated by the green LED. In this mode, the outputs will remain in the last valid output state.

Note:

If the option for synchronization is not used, the synchronization input has to be connected to ground (0 V) or the sensor must be operated via a V1 cordset (4-pin).

The synchronization function cannot be activated during programming mode and vice versa.

The following synchronization modes are possible:

- 1. Several sensors (max. number see technical data) can be synchronized together by interconnecting their respective synchronization inputs. In this case, each sensor alternately transmits ultrasonic pulses in a self multiplexing mode. No two sensors will transmit pulses at the same time (see note below).
- 2. Multiple sensors can be controlled by the same external synchronization signal. In this mode the sensors are triggered in parallel and are synchronized by a common external synchronization pulse.
- 3. A separate synchronization pulse can be sent to each individual sensor. In this mode the sensors operate in external multiplex mode (see note
- 4. A high level (+U_B) on the synchronization input switches the sensor to standby mode.


104093_eng.xml

Date of issue: 2016-08-01

Sensor response times will increase proportionally to the number of sensors that are in the synchronization string. This is a result of the multiplexing of the ultrasonic transmit and receive signal and the resulting increase in the measurement cycle time.

Note on communication with the UC-30GM-R2 interface cable

The UC-30GM-R2 interface cable allows for communication with the ultrasonic sensor using ULTRA3000 software. The cable creates a connection between a PC RS-232 interface and the programming plug socket on the sensor. When connecting to the sensor, make certain the plug is lined up correctly; otherwise no communication will be possible. The key of the cable's plug must be aligned to the groove of the socket on the sensor (not with the arrow symbol on the sensor).



Programmable parameters with the ULTRA3000 software

- Evaluation limits A1 and A2
- Operation mode
- Sonic speed
- Temperature offset (The inherent temperature-rise of the sensor can be considered in the temperature compensation)
- Expansion of the unusable area (for suppression of unusable area echoes)
- Reduction of the detection range (for suppression of remote range echoes)
- Time of measuring cycle
- Acoustic power (interference of the burst duration)
- Sensitivity
- Behavior of the sensor in case of echo loss
- Behavior of the sensor in case of a fault
- Average formation via an allowed number of measuring cycles
- Selection of the parameter set, RS 232 or manually

Note:

When connected to a PC and running the ULTRA3000 software, the sensor can act as a long term data logger as well.

Installation conditions

If the sensor is installed in an environment where the temperature can fall below 0 °C, one of these mounting flanges must be used for mounting: BF30, BF30-F, or BF 5-30.

If the sensor is mounted in a through hole using the included steel nuts, it must be mounted at the middle of the threaded housing. If it must be mounted at the front end of the threaded housing, plastic nuts with centering ring (optional accessories) must be used.