The STV 25K DIN Rail Series - Surge Protective Devices

This series provides point-of-use protection, at the dedicated equipment level, against damaging transients. Ideal for installation in electronic control cabinets found in harsh industrial environments such as the factory floor or at remote locations. These devices provide 50,000 amps of surge protection, sinewave tracking, LED status indication and form "C" dry contacts. This DIN Rail series also provides protection on all electrical paths and comes with a standard ten year product warranty.

Applications (20 Amp Max)

- Control Cabinets for Industrial Automation
- Point-of-Use Industrial/Service Equipment
- Remote Commercial or Industrial Equipment
- Instrumentation and Large Test Equipment
- Commercial and Building Automation Systems

Features

- Compact and narrow design maximizes panel space.
- Low clamping levels for more effective protection.
- Easy access terminal screws for quick mounting and installation.
- 50,000 amps of surge protection.
- Sine wave tracking and all mode protection provide consistent and reliable protection on all electrical paths.
- Thermal fusing prevents MOV overheating caused by excessive current levels.

Certifications and Compliances

- c **Plus** UL Recognized Component
 - UL 1449, 3rd Edition, type 4 locations
 - UL 1283
- RoHS Compliant

Related Products

- DIN Rail Power Supplies
- DIN Rail AC UPS
- Industrial Control Transformers
- Line Reactors
- Active Tracking® Filters






Selection Table

Catalog Number	Input Voltage	
STV 25K-10S	120 V	Single Phase (L - N)
STV 25K-24S	240 V	Single Phase (L1 - L2)

Dimensional Diagram - in. (mm)



STV 25K Specifications

Description	Catalog Number		
	STV 25K–10S	STV 25K–24S	
Input Voltage	120 Vac, Single Phase 0-135 Vrms	240 Vac, Single Phase 0-260 Vrms	
Maximum Continuous Operating Voltage (MCOV)	120 - 150 Vrms	240 - 275 Vrms	
Line Frequency	47-63 Hz		
Connection/Mounting Type	DIN Rail Mount (Chassis Mount Bracket Optional order SDN-PMBRK2) with screw terminals for #12 AWG.		
Input Current Rating	20 Amps		
Phase Configuration	2 wire + GND		
Weight – Ibs (kg)	3.0 lbs (1.36 kg)		
Dimensions H x W x D – in (mm)	4.87 x 2.56 x 4.75 (123.7 x 65.0 x 120.7) includes mounting bracket		
Modes of Protection	All Mode: L - N, L - L, L - G, N-G		
Status Indication	Green LED, Form C Contacts		
Packaging	Metal DIN Rail Mount Enclosure, IP20		
Response Time	< 0.5 nsec		
Operating Temperature	-40°C to +60°C		
Operating Humidity	0% to 95% Non-condensing		
	Noise Attenuation		
Normal Mode Common Mode	50 dB Min 40 dB Min UL 1449, 3 rd Edition, Type 4 Voltage Protection Ratings (VPRs) Vpeak		
L – N L – L L – G N – G	500 500 500	900 900 	
	Peak Surge Current Capability		
Warranty	10 year limited warranty		

1