

# SKM 400GA123D



**SEMITRANS® 4**

## IGBT Modules


**SKM 400GA123D**

### Features

- MOS input (voltage controlled)
- N channel, homogeneous Si
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to  $6 \times I_{Cnom}$
- Latch-up free
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (12 mm) and creepage distances (20 mm)

### Typical Applications

- Switching (not for linear use)



**GA**

| Absolute Maximum Ratings |  | $T_C = 25\text{ }^\circ\text{C}$ , unless otherwise specified |      |                  |
|--------------------------|--|---|------|------------------|
| Symbol                   | Conditions   | Values  |      | Units            |
| <b>IGBT</b>              |  |   |      |                  |
| $V_{CES}$                | $T_j = 25\text{ }^\circ\text{C}$   | 1200  |      | V                |
| $I_C$                    | $T_j = 150\text{ }^\circ\text{C}$  | $T_{case} = 25\text{ }^\circ\text{C}$                         | 400  | A                |
|                          |  | $T_{case} = 80\text{ }^\circ\text{C}$                         | 360  | A                |
| $I_{CRM}$                | $I_{CRM} = 2 \times I_{Cnom}$  | 600   |      | A                |
| $V_{GES}$                |  | $\pm 20$  |      | V                |
| $t_{psc}$                | $V_{CC} = 600\text{ V}; V_{GE} \leq 20\text{ V}; T_j = 125\text{ }^\circ\text{C}$<br>$V_{CES} < 1200\text{ V}$ | 10  |      | $\mu\text{s}$    |
| <b>Inverse Diode</b>     |  |   |      |                  |
| $I_F$                    | $T_j = 150\text{ }^\circ\text{C}$  | $T_{case} = 25\text{ }^\circ\text{C}$                         | 390  | A                |
|                          |  | $T_{case} = 80\text{ }^\circ\text{C}$                         | 260  | A                |
| $I_{FRM}$                | $I_{FRM} = 2 \times I_{Fnom}$  | 600   |      | A                |
| $I_{FSM}$                | $t_p = 10\text{ ms}; \text{sin.}$  | $T_j = 150\text{ }^\circ\text{C}$                             | 2880 | A                |
| <b>Module</b>            |  |   |      |                  |
| $I_{t(RMS)}$             |  | 500   |      | A                |
| $T_{vj}$                 |  | - 40 ... + 150  |      | $^\circ\text{C}$ |
| $T_{stg}$                |  | - 40 ... + 125  |      | $^\circ\text{C}$ |
| $V_{isol}$               | AC, 1 min.   | 2500  |      | V                |

| Characteristics |   | $T_C = 25\text{ }^\circ\text{C}$ , unless otherwise specified   |      |       |                  |
|-----------------|---|---|------|-------|------------------|
| Symbol          | Conditions                                      | min.  | typ. | max.  | Units            |
| <b>IGBT</b>     |   |   |      |       |                  |
| $V_{GE(th)}$    | $V_{GE} = V_{CE}, I_C = 12\text{ mA}$           | 4,5   | 5,5  | 6,5   | V                |
| $I_{CES}$       | $V_{GE} = 0\text{ V}, V_{CE} = V_{CES}$         |   | 0,1  | 0,3   | mA               |
| $V_{CE0}$       |   | $T_j = 25\text{ }^\circ\text{C}$                                | 1,4  | 1,6   | V                |
|                 |   | $T_j = 125\text{ }^\circ\text{C}$                               | 1,6  | 1,8   | V                |
| $r_{CE}$        | $V_{GE} = 15\text{ V}$                          | $T_j = 25\text{ }^\circ\text{C}$                                | 3,66 | 4,66  | $\text{m}\Omega$ |
|                 |   | $T_j = 125\text{ }^\circ\text{C}$                               | 5    | 6,33  | $\text{m}\Omega$ |
| $V_{CE(sat)}$   | $I_{Cnom} = 300\text{ A}, V_{GE} = 15\text{ V}$ |   | 2,5  | 3     | V                |
| $C_{ies}$       |   |   | 22   | 30    | nF               |
| $C_{oes}$       | $V_{CE} = 25, V_{GE} = 0\text{ V}$              |   | 3,3  | 4     | nF               |
| $C_{res}$       |   |   | 1,2  | 1,6   | nF               |
| $Q_G$           | $V_{GE} = -8\text{ V} - +20\text{ V}$           |   | 3000 |       | nC               |
| $R_{Gint}$      | $T_j = \text{ }^\circ\text{C}$                  |   | 1,25 |       | $\Omega$         |
| $t_{d(on)}$     | $R_{Gon} = 3,3\ \Omega$                         | $V_{CC} = 600\text{ V}$<br>$I_C = 300\text{ A}$                 | 200  | 400   | ns               |
| $t_r$           |   |   | 115  | 220   | ns               |
| $E_{on}$        |   |   | 38   |       | mJ               |
| $t_{d(off)}$    | $R_{Goff} = 3,3\ \Omega$                        | $T_j = 125\text{ }^\circ\text{C}$<br>$V_{GE} = \pm 15\text{ V}$ | 720  | 900   | ns               |
| $t_f$           |   |   | 80   | 100   | ns               |
| $E_{off}$       |   |   | 40   |       | mJ               |
| $R_{th(j-c)}$   | per IGBT  |   |      | 0,045 | K/W              |



**SEMITRANS® 4**

## IGBT Modules


**SKM 400GA123D**

### Features

- MOS input (voltage controlled)
- N channel, homogeneous Si
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to  $6 \times I_{cnom}$
- Latch-up free
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (12 mm) and creepage distances (20 mm)

### Typical Applications

- Switching (not for linear use)



GA

| Characteristics           |  |   | min. | typ.      | max.  | Units |
|---------------------------|--|---|------|-----------|-------|-------|
| Symbol                    | Conditions                                       |   |      |           |       |       |
| <b>Inverse Diode</b>      |  |   |      |           |       |       |
| $V_F = V_{EC}$            | $I_{Fnom} = 300 \text{ A}; V_{GE} = 0 \text{ V}$ | $T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$  |      | 2         | 2,5   | V     |
|                           |  | $T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$ |      | 1,8       |       | V     |
| $V_{F0}$                  |  | $T_j = 25 \text{ }^\circ\text{C}$             |      | 1,1       | 1,2   | V     |
|                           |  | $T_j = 125 \text{ }^\circ\text{C}$            |      |           |       | V     |
| $r_F$                     |  | $T_j = 25 \text{ }^\circ\text{C}$             |      | 3         | 4,3   | mΩ    |
|                           |  | $T_j = 125 \text{ }^\circ\text{C}$            |      |           |       | mΩ    |
| $I_{RRM}$                 | $I_F = 300 \text{ A}$                            | $T_j = 25 \text{ }^\circ\text{C}$             |      | 85        |       | A     |
| $Q_{rr}$                  | $di/dt = 2000 \text{ A}/\mu\text{s}$             |   |      | 13        |       | μC    |
| $E_{rr}$                  | $V_{GE} = 0 \text{ V}; V_{CC} = 600 \text{ V}$   |   |      |           |       | mJ    |
| $R_{th(j-c)D}$            | per diode  |   |      |           | 0,125 | K/W   |
| <b>Freewheeling Diode</b> |  |   |      |           |       |       |
| $V_F = V_{EC}$            | $I_{Fnom} = \text{A}; V_{GE} = \text{V}$         | $T_j = \text{ }^\circ\text{C}_{chiplev.}$     |      |           |       | V     |
| $V_{F0}$                  |  | $T_j = 25 \text{ }^\circ\text{C}$             |      |           |       | V     |
|                           |  | $T_j = 125 \text{ }^\circ\text{C}$            |      |           |       | V     |
| $r_F$                     |  | $T_j = 25 \text{ }^\circ\text{C}$             |      |           |       | V     |
|                           |  | $T_j = 125 \text{ }^\circ\text{C}$            |      |           |       | V     |
| $I_{RRM}$                 | $I_F = \text{A}$                                 | $T_j = \text{ }^\circ\text{C}$                |      |           |       | A     |
| $Q_{rr}$                  |  |   |      |           |       | μC    |
| $E_{rr}$                  | $V_{GE} = 0 \text{ V}; V_{CC} = 600 \text{ V}$   |   |      |           |       | mJ    |
|                           | per diode  |   |      |           |       | K/W   |
| <b>Module</b>             |  |   |      |           |       |       |
| $L_{CE}$                  |  |   |      | 15        | 20    | nH    |
| $R_{CC+EE}$               | res., terminal-chip                              | $T_{case} = 25 \text{ }^\circ\text{C}$        |      | 0,18      |       | mΩ    |
|                           |  | $T_{case} = 125 \text{ }^\circ\text{C}$       |      | 0,22      |       | mΩ    |
| $R_{th(c-s)}$             | per module                                       |   |      |           | 0,038 | K/W   |
| $M_s$                     | to heat sink M6                                  |   |      | 3         | 5     | Nm    |
| $M_t$                     | to terminals M6 (M4)                             |   |      | 2,5 (1,1) | 5 (2) | Nm    |
| w                         |  |   |      |           | 330   | g     |

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.

# SKM 400GA123D



**SEMITRANS® 4**

## IGBT Modules


**SKM 400GA123D**

### Features

- MOS input (voltage controlled)
- N channel, homogeneous Si
- Low inductance case
- Very low tail current with low temperature dependence
- High short circuit capability, self limiting to  $6 \times I_{cnom}$
- Latch-up free
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (12 mm) and creepage distances (20 mm)

### Typical Applications

- Switching (not for linear use)



**GA**


| $Z_{th}$                         |         | Conditions | Values | Units |
|----------------------------------|---------|------------|--------|-------|
| <b><math>Z_{th(j-c)I}</math></b> |         |            |        |       |
| $R_{\theta j-c}$                 | $i = 1$ |            | 33     | mk/W  |
| $R_{\theta j-c}$                 | $i = 2$ |            | 8,8    | mk/W  |
| $R_{\theta j-c}$                 | $i = 3$ |            | 2,6    | mk/W  |
| $R_{\theta j-c}$                 | $i = 4$ |            | 0,6    | mk/W  |
| $\tau_{th(j-c)}$                 | $i = 1$ |            | 0,05   | s     |
| $\tau_{th(j-c)}$                 | $i = 2$ |            | 0,009  | s     |
| $\tau_{th(j-c)}$                 | $i = 3$ |            | 0,0024 | s     |
| $\tau_{th(j-c)}$                 | $i = 4$ |            | 0,0001 | s     |
| <b><math>Z_{th(j-c)D}</math></b> |         |            |        |       |
| $R_{\theta j-c}$                 | $i = 1$ |            | 85     | mk/W  |
| $R_{\theta j-c}$                 | $i = 2$ |            | 31     | mk/W  |
| $R_{\theta j-c}$                 | $i = 3$ |            | 7,8    | mk/W  |
| $R_{\theta j-c}$                 | $i = 4$ |            | 1,2    | mk/W  |
| $\tau_{th(j-c)}$                 | $i = 1$ |            | 0,0537 | s     |
| $\tau_{th(j-c)}$                 | $i = 2$ |            | 0,0086 | s     |
| $\tau_{th(j-c)}$                 | $i = 3$ |            | 0,003  | s     |
| $\tau_{th(j-c)}$                 | $i = 4$ |            | 0,0001 | s     |

# SKM 400GA123D


UL Recognized

CASED59

File 63 532



Case D 59



GA

Case D 59