

# SKKT 273; SKKH 273



**SEMIPACK® 3**

## Thyristor / Diode Modules

**SKKT 273**

**SKKH 273**

### Preliminary Data

### Features

- Industrial standard package
- Electrically insulated base plate
- Heat transfer through aluminum oxide ceramic insulated metal base plate
- Chip soldered on direct copper bonded Al<sub>2</sub>O<sub>3</sub> ceramic
- Thyristor with center gate
- UL recognition applied for file no. E63532


### Typical Applications

- DC motor control (e. g. for machine tools)
- Temperature control (e. g. for ovens, chemical processes)
- Professional light dimming (studios, theaters)

1) See the assembly instructions







| $V_{RSM}$<br>V | $V_{RRM}, V_{DRM}$<br>V | $I_{TRMS} = 450$ A (maximum value for continuous operation)<br>$I_{TAV} = 273$ A (sin. 180; $T_c = 85$ °C) |              |
|----------------|-------------------------|--|--------------|
| 1300           | 1200                    | SKKT 273/12E   | SKKH 273/12E |
| 1700           | 1600                    | SKKT 273/16E   | SKKH 273/16E |

| Symbol           | Conditions  | Values                 | Units                                |
|------------------|---|------------------------|--------------------------------------|
| $I_{TAV}$        | sin. 180; $T_c = 85$ (100) °C;                                      | 273 (202)              | A                                    |
| $I_{TSM}$        | $T_{vj} = 25$ °C; 10 ms<br>$T_{vj} = 130$ °C; 10 ms                 | 9000<br>8000           | A<br>A                               |
| $i^2t$           | $T_{vj} = 25$ °C; 8,3 ... 10 ms<br>$T_{vj} = 130$ °C; 8,3 ... 10 ms | 405000<br>320000       | A <sup>2</sup> s<br>A <sup>2</sup> s |
| $V_T$            | $T_{vj} = 25$ °C; $I_T = 750$ A                                     | max. 1,6               | V                                    |
| $V_{T(TO)}$      | $T_{vj} = 130$ °C   | max. 0,9               | V                                    |
| $r_T$            | $T_{vj} = 130$ °C   | max. 0,92              | mΩ                                   |
| $I_{DD}; I_{RD}$ | $T_{vj} = 130$ °C; $V_{RD} = V_{RRM}; V_{DD} = V_{DRM}$             | max. 100               | mA                                   |
| $t_{gd}$         | $T_{vj} = 25$ °C; $I_G = 1$ A; $di_G/dt = 1$ A/μs                   | 1                      | μs                                   |
| $t_{gr}$         | $V_D = 0,67 * V_{DRM}$  | 2                      | μs                                   |
| $(di/dt)_{cr}$   | $T_{vj} = 130$ °C   | max. 130               | A/μs                                 |
| $(dv/dt)_{cr}$   | $T_{vj} = 130$ °C   | max. 1000              | V/μs                                 |
| $t_q$            | $T_{vj} = 130$ °C, typ.   | 150                    | μs                                   |
| $I_H$            | $T_{vj} = 25$ °C; typ. / max.                                       | 150 / 500              | mA                                   |
| $I_L$            | $T_{vj} = 25$ °C; $R_G = 33$ Ω; typ. / max.                         | 300 / 2000             | mA                                   |
| $V_{GT}$         | $T_{vj} = 25$ °C; d.c.  | min. 2                 | V                                    |
| $I_{GT}$         | $T_{vj} = 25$ °C; d.c.  | min. 150               | mA                                   |
| $V_{GD}$         | $T_{vj} = 130$ °C; d.c.   | max. 0,25              | V                                    |
| $I_{GD}$         | $T_{vj} = 130$ °C; d.c.   | max. 10                | mA                                   |
| $R_{th(j-c)}$    | cont.; per thyristor / per module                                   | 0,104 / 0,052          | K/W                                  |
| $R_{th(j-c)}$    | sin. 180; per thyristor / per module                                | 0,108 / 0,054          | K/W                                  |
| $R_{th(j-c)}$    | rec. 120; per thyristor / per module                                | 0,122 / 0,061          | K/W                                  |
| $R_{th(c-s)}$    | per thyristor / per module  | 0,08 / 0,04            | K/W                                  |
| $T_{vj}$         |   | - 40 ... + 130         | °C                                   |
| $T_{stg}$        |   | - 40 ... + 125         | °C                                   |
| $V_{isol}$       | a. c. 50 Hz; r.m.s.; 1 s / 1 min.                                   | 3600 / 3000            | V~                                   |
| $M_s$            | to heatsink   | 5 ± 15 % <sup>1)</sup> | Nm                                   |
| $M_t$            | to terminals  | 9 ± 15 %               | Nm                                   |
| $a$              |   | 5 * 9,81               | m/s <sup>2</sup>                     |
| $m$              | approx.   | 410                    | g                                    |
| Case             | SKKT<br>SKKH  | A 43a<br>A 56a         |                                      |












SKKT

SKKH



# SKKT 273; SKKH 273





This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.