SKKT 27, SKKT 27B, SKKH 27



SEMIPACK[®] 1

Thyristor / Diode Modules

SKKT 27 SKKT 27B SKKH 27

Features


- Heat transfer through aluminium oxide ceramic isolated metal baseplate
- Hard soldered joints for high reliability
- UL recognized, file no. E 63 532

Typical Applications


- DC motor control (e. g. for machine tools)
- · AC motor soft starters
- Temperature control (e. g. for ovens, chemical processes)
- Professional light dimming (studios, theaters)
- 1) See the assembly instructions


V _{RSM}	V _{RRM} , V _{DRM}	I _{TRMS} = 50 A (maximum value for continuous operation)		
V	V	I _{TAV} = 27 A (sin. 180; T _c = 82 °C)		
900	800	SKKT 27/08E	SKKT 27B08E	SKKH 27/08E
1300	1200	SKKT 27/12E	SKKT 27B12E	SKKH 27/12E
1500	1400	SKKT 27/14E	SKKT 27B14E	SKKH 27/14E
1700	1600	SKKT 27/16E	SKKT 27B16E	SKKH 27/16E
1900	1800			SKKH 27/18E

Symbol	Conditions	Values	Units
I _{TAV}	sin. 180; T _c = 85 (100) °C	25 (18)	Α
I _D	P3/180; T _a = 45 °C; B2 / B6	38 / 50	Α
	P3/180F; T _a = 35 °C; B2 / B6	60 /77	Α
$I_{\rm RMS}$	P3/180; T _a = 45 °C; W1 / W3	52 / 3 x 37	Α
I _{TSM}	T _{vj} = 25 °C; 10 ms	550	Α
	$T_{vj} = 125 ^{\circ}\text{C}; 10 \text{ms}$	480	Α
i²t	$T_{vj} = 25 ^{\circ}\text{C}; 8,3 \dots 10 \text{ms}$	1500	A²s
	T _{vj} = 125 °C; 8,3 10 ms	1150	A²s
V _T	T _{vj} = 25 °C; I _T = 75 A	max. 1,8	V
$V_{T(TO)}$	T _{vj} = 125 °C	max. 0,9	V
r_T	T _{vj} = 125 °C	max. 12	mΩ
$I_{DD}; I_{RD}$	T_{vj} = 125 °C; V_{RD} = V_{RRM} ; V_{DD} = V_{DRM}	max. 10	mA
t _{gd}	$T_{vj} = 25 \text{ °C; } I_G = 1 \text{ A; } di_G/dt = 1 \text{ A/}\mu\text{s}$	1	μs
t _{gr}	$V_{D} = 0.67 * V_{DRM}$	1	μs
(di/dt) _{cr}	T _{vi} = 125 °C	max. 150	A/µs
(dv/dt) _{cr}	T _{vi} = 125 °C	max. 1000	V/µs
t _q	T _{vi} = 125 °C	80	μs
I _H	T_{vj} = 25 °C; typ. / max.	100 / 200	mA
I_{L}	T_{vj} = 25 °C; R_G = 33 Ω ; typ. / max.	250 / 400	mA
V _{GT}	T _{vj} = 25 °C; d.c.	min. 3	V
I _{GT}	$T_{vj} = 25 ^{\circ}\text{C}; \text{d.c.}$	min. 150	mA
V_{GD}	$T_{vj} = 125 ^{\circ}\text{C}; \text{d.c.}$	max. 0,25	V
I_{GD}	$T_{vj} = 125 ^{\circ}\text{C}; \text{d.c.}$	max. 5	mA
R _{th(j-c)}	cont.; per thyristor / per module	0,9 / 0,45	K/W
R _{th(j-c)}	sin. 180; per thyristor / per module	0,95 / 0,48	K/W
R _{th(j-c)}	rec. 120; per thyristor / per module	1 / 0,5	K/W
$R_{th(c-s)}$	per thyristor / per module	0,2 / 0,1	K/W
T_{vj}		- 40 + 125	°C
T _{stg}		- 40 + 125	°C
V _{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3600 / 3000	V~
M _s	to heatsink	5 ± 15 % ¹⁾	Nm
M_t	to terminals	3 ± 15 %	Nm
а		5 * 9,81	m/s²
m	approx.	95	g
Case	SKKT	A 46	
	SKKTB	A 48	
	SKKH	A 47	



SKKT 27, SKKT 27B, SKKH 27





This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.