

SDU DIN Rail DC UPS Series

The SDU DIN Rail DC UPS is an advanced 24 Vdc uninterruptible power system that combines an industry leading design with a wide operational temperature range and unique installation options. The SDU DC UPS is a powerful, microprocessor controlled UPS that provides protection from power interruptions. With an input voltage range of 22.5 to 30.0 Vdc, the DC UPS is the ideal power back-up solution for your critical connected

These units were designed specifically for use with SolaHD's popular SDN Series of power supplies. SolaHD's external battery module is the only one on the market that allows you to seal the electronics in the panel and maintain safety by placing the battery outside of a nonventilated enclosure.

These units include easy to wire screw terminations for critical devices needing battery back-up. The SDU DC UPS includes an automatic self-test feature that checks the UPS and battery functions. Battery charging occurs automatically when input DC power is applied. When power fails, the DC UPS will switch to battery back-up. If the battery is no longer useful, the UPS will sound an alarm and an LED indicator will illuminate.

Back-up power protection in modern industrial applications depends mainly on AC UPS. AC is converted to DC, and converted back to AC in the AC UPS, then converted back to DC in the protected equipment power supply. By applying the new SolaHD SDU DIN Rail DC UPS, you avoid the inefficiencies of all these conversions. This design maximizes system up-time flexibility, and optimizes reliability assurance.





Features

- Modular, rugged industrial grade design
- Microprocessor based controls
- Automatic self-test feature for UPS function and battery management check
- Power module wide operation temperature range (-20 to +50°C)
- Flexible batteries back-up expansion capabilities
- Overload protection in normal and battery modes
- User replaceable batteries
- Both power and battery modules are UL508 Listed
- IP-20 rated input and output screw terminals No internal fan, no extra cooling required
- · Sturdy, reliable all metal DIN Rail mounting connector
- LED Status Indicators
- · Universal Dry Contact Relay terminals provide remote signaling
- Monitoring, diagnostics, and remote turn-on and shut-off capabilities

Approx.

· Limited two-year warranty

Applications

- Industrial/Machine Control
- Automation Process Control Computer-based Control Systems
- · Conveying Equipment Material Handling
- · Packaging Machines
- Semiconductor fabrication equipment
- DeviceNet
- · Amusement Park Equipment Pharmaceutical Applications
- · Control Rooms

Related Products

- SDN-P Series DIN Rail Power Supplies
- SDN-C Series DIN Rail Power Supplies • STV 25K Series Surge Protection

Selection

Catalog Number	Description	Ship Weight Ibs (kg)
SDU 10-24	240 VA, 24V/10A DIN Rail DC UPS power module, battery module is required	1.65 (0.65)
SDU 20-24	480 VA, 24V/20A DIN Rail DC UPS power module, battery module is required	1.65 (0.65)
SDU 24-BAT	24V DIN Rail/Panel Mount Battery Module (cable included)	12.0 (5.33)
SDU 24-BATEM	24V External Mount Battery Module (cable included)	16.0 (7.11)
SDU 24EXTBC6	Optional 6 ft. Battery Module cable to 24V DC UPS	0.5 (0.22)
SDU 24-DB9	Optional interface kit to convert relay contacts signals to DB9 signals	1.0 (0.45)
SDU-PMBRK	Optional chassis mount brackets to secure UPS to wall, panel, or enclosure	0.5 0 (.22)

There are three individual hardware products when putting an SDU DC UPS system into operation:

- 1. 24 Vdc Power Supply (Recommended SolaHD SDN Series) 2. 24 Vdc SDU DC UPS Power Module
- 3. 24 Vdc SDU DC UPS Battery Module; or 24 Vdc SDU DC UPS External Battery Module

There are two models of the SDU DC UPS Power Module: 1. SDU 10-24, 24 Vdc/10amp (battery modules are required)


modules can be connected to the SDU DC UPS.

Battery Options

- 2. SDU 20-24, 24 Vdc/20amp (battery modules are required) There are two models* of the SDU DC UPS Battery Modules:
 - 2. SDU 24-BATEM, Panel mount, alternate battery module for external installation of nonventilated enclosures, only 1 battery module can be connected to the SDU DC UPS.

1. SDU 24-BAT, DIN Rail/Panel mount for installation in ventilated enclosure, up to 4 battery

*Can not use a combination of both models of the battery modules, only one model of the battery module can be connected to the SDU DC UPS.



DIN Rail Mounted Battery

External Battery

AC/DC Power Supply
 Power Module: SDU 10-24 or SDU 20-24
 Battery Module: SDU 24-BAT
 Optional battery module for extended Back-up.

AC/DC Power Supply
 Power Module: SDU 10-24 or SDU 20-24
 Battery Module: SDU 24-BATEM

Specifications 🚹 Тор

Catalog Number	SDU 10-24	SDU 20-24		
	Input Voltage			
Input Nominal	24	Vdc		
Voltage Input Voltage	22 5 -	30 Vdc		
Range Input Fuse		se 30A		
Triput ruse	Output	SE SUA		
Name in al Outrout	·			
Nominal Output Voltage	24	Vdc		
Output Voltage Range	22.5 -	30 Vdc		
Output Current	10A	20A		
Current Limit	12A	22A		
	Protection			
Input Protection	Fuse for overload & s	hort circuit protection		
Overload	Electrical Circ	uit Protection		
Protection Short Circuit	UPS output cut	off immediately		
	Battery Module			
Туре	Sealed maintenance-f	ree lead acid batteries		
Charging Current		5 A		
Typical Recharge	O Haven for 4.1	Rattery Modulo		
Time (to 90% of full	24 Hours for 2	Battery Module Battery Module litional Battery Module		
capacity) Back-up Time	14 minutes	4 minutes		
(full load) *		tage drops below 22V to prevent		
Protection	the complete depletion of the battery,			
	Physical			
Net Weight - lbs (kg)	1.65 ((0.75)		
Dimensions H x W x D - in. (mm)	4.88 x 3.02 x 4.55	5 (124 x 77 x 116)		
x 2 ()	Alarm			
Battery Low	Danid Audible India	ator every 1 second		
Battery Low	Rapid Addible Hidio	ator every i second		
Overload	Continuous Au	idible Indicator		
	Environment			
Audible Noise	<40 dBA (1 met	er from surface)		
Power Module				
Operating Temperature	-20 degrees C to	o +50 degrees C		
Storage	20 dogwood C t	2. 70 degrees C		
Temperature	-20 degrees C to	o +70 degrees C		
Humidity	0-95%			
	U-95%			
Max Elevation	3500 meters	(11,483 feet)		
Shock & Vibration	ock & Vibration According to ISTA 2A			
	DC UPS System** Safe	ety		
US Standard	UL 60950-1, UL508,	FCC Part 15, Class A		
Canadian Standard	CAN/CSA C22.2 No 107.1-01,	CAN/CSA C22.2 No. 60950-1		
		C 60950-1 (CB Scheme)		
CE	-			
	Directive 2004/108/EC: EN 62040-2 Category Class A (2005), IEC 61000-3-2, IEC 61000	0-4-2, IEC 61000-4-3, IEC 61000-4-4, IEC		
	61000-4-5, IEC 61000-4-6 + A1 General	, IEC 61000-4-8, IEC 61000-2-2		
MTBF	> 200,000 Hours, M	IIL-STD HDBK-217F		
	Installation			
	Outputs are capable of providing high curr	ents for short periods of time for inductive		
Output	load startup Fusing may be required for wire/loads if	or switching.		
	toler	ated.		
Mounting	Simple snap-on system for DIN Rail TS35/7			
0	screw mounting Input & Output: IP20-rated screw terminals			
Connections		n2)		
Relay Contact	·	ze range: 24-16 AWG (0.34-4mm2)		
Connections				
Case	Fully enclosed metal housing with vent	tilation grid to keep out small particles.		

Notes:

Free Space

See Battery Back-up Times below.
 DC UPS System includes one power module (SDU 10-24 or SDU 20-24) and one or more battery modules (SDU 24-BAT or SDU 24BATEM).

20 mm above and 35 mm below, 20 mm left and right, 10 mm in front

Battery Module Specifications



Parameter	SDU 24-BAT	SDU 24-BATEM		
Nominal Voltage	24 Vdc			
Protection	Fuse: 30A	Circuit Breaker: 24V, 25A		
Charging Current	0.5A	0.8A		
Enclosure Dimension in. (mm)	4.88 x 8.27 x 4.55 (124 x 210 x 116)	11.5 x 5.57 x 4.57 (292 x 142 x 116)		
Enclosure Type	IP20	NEMA 1		
Terminal Connector Type	Polarized Powerpole Connectors			
Batteries	Replaceable Batteries			
Accessories	1 ft. polarized battery cable	6 ft. polarized battery cable		
Operating Temperature	-20 degrees C to +50 degrees C			
Storage Temperature	-20 degrees C to +40 degrees C			
Humidity	95% no condensation			
Safety Standard for DC UPS System*	UL60950-1, IEC 60950-1, UL508, CE CAN/CSA C22.2 No 107.1-01 CAN/CSA C22.2 No 60950-1			
Weight - Ibs (kg)	12 (5.33)	16 (7.11)		
Mounting	Simple snap-on system for DIN Rail TS35/7.5 or TS35/15 or chassis- mounted, optional screw mounting set SDU-	Wall/Chassis Mounting		

PMBRK.

SDU 10-24 with SDU 24-BAT							
Load	20% (2A)	40% (4A)	60% (6A)	80% (8A)	100% (10A)		
1 unit	113	45	30	21	14		
2 units	247	114	74	48	38		
3 units	396	178	117	80	58		
4 units	531	233	148	111	81		
	SDU	10-24 with	SDU 24-B	ATEM			
1 EPB	135	52	28	19	14		
	SDU	J 20-24 wi	th SDU 24	ВАТ			
Load	20% (4A)	40% (8A)	60% (12A)	80% (16A)	100% (20A)		
1 unit	46	21	10	06	04		
2 units	116	50	28	17	10		
3 units	178	80	46	31	20		
4 units	237	113	65	43	31		
	SDU	20-24 with	SDU 24-B	ATEM			
1 EBPS	48	17	9	6	1		

What's New | Products | Cross Reference | Technical Support | Contact Us | Search | UPS Home