


Stainless Steel Low Profile Vandal Resistant - Momentary


FRONT PANEL MOUNTING MP0027

- 28mm diameter
- S.P.C.O. Microswitch
- 5A, 250V a.c.






- Front Panel Sealed to IP66
- 28mm diameter
- S.P.C.O. Microswitch
- 5A, 250V a.c.





- 22mm diameter
- S.P.C.O. Microswitch
- 5A, 250V a.c.



Specification	MP0027	MP0038	MP0025
Terminations:	Solder Tags	Solder Tags	Solder Tags
Switching:	S.P.C.O. Momentary Action (Microswitch)	S.P.C.O. Momentary Action (Microswitch)	S.P.C.O. Momentary Action (Microswitch)
Max. Rating:	5A, 250V a.c.	5A, 250V a.c.	5A, 250V a.c.
Contact Resistance:	<10mΩ	<10mΩ	<10mΩ
Insulation Resistance:	$> 10^3 M\Omega$	$> 10^3 M\Omega$.	$> 10^3 M\Omega$
Dielectric Strength:	>2.0kV a.c.	>2.0kV a.c.	>2.0kV a.c.
Operating Temp. Range:	–20°C to +70°C	-20°C to +70°C	-20°C to +70°C
Sealing (Front of panel only):		Protection Classification: IP66 EN60529 1992 (Micro switch not sealed)	
Operations Mechanical: Electrical:	1,000,000 (min) 35,000 (min)	1,000,000 (min) 35,000 (min)	1,000,000 (min) 35,000 (min)
Operating Pressure:	7.5N (typ)	12.5N (typ)	6.1N (typ)
Rear Nut Fixing Torque:	2.5Nm	1.13Nm	-
Materials Mouldings: Tags/Terminations: Switch Body & Button:	Glass Filled Nylon Brass, Tin Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel	Glass Filled Nylon Brass, Tin Plated Stainless Steel
Contacts:	Fine Silver	Fine Silver	Fine Silver
Variants:	Engraved Button, Non-Rotating Button, details on request	Engraved Button, Non-Rotating Button, details on request	Engraved Button, Non-Rotating Button, details on request
RoHS	Compliant	Compliant	Compliant