Preferred Device

# **Sensitive Gate Triacs**

## Silicon Bidirectional Thyristors

Designed primarily for full-wave AC control applications, such as light dimmers, motor controls, heating controls and power supplies; or wherever full-wave silicon gate controlled solid-state devices are needed. Triac type thyristors switch from a blocking to a conducting state for either polarity of applied anode voltage with positive or negative gate triggering.

#### Features

- Sensitive Gate Triggering Uniquely Compatible for Direct Coupling to TTL, HTL, CMOS and Operational Amplifier Integrated Circuit Logic Functions
- Gate Triggering: 4 Mode 2N6071A, B; 2N6073A, B; 2N6075A, B
- Blocking Voltages to 600 V
- All Diffused and Glass Passivated Junctions for Greater Parameter Uniformity and Stability
- Small, Rugged, Thermopad Construction for Low Thermal Resistance, High Heat Dissipation and Durability
- Device Marking: Device Type, e.g., 2N6071A, Date Code




## **ON Semiconductor®**

http://onsemi.com

TRIACS 4.0 A RMS, 200 – 600 V



## MARKING DIAGRAM



#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 7 of this data sheet.

Preferred devices are recommended choices for future use and best overall value.

\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### **MAXIMUM RATINGS** (T<sub>J</sub> = $25^{\circ}$ C unless otherwise noted)

Rating	Symbol	Value	Unit
*Peak Repetitive Off-State Voltage (Note 1) ( $T_J = -40$ to 110°C, Sine Wave, 50 to 60 Hz, Gate Open) 2N6071A,B 2N6073A,B 2N6075A,B	V <sub>drm,</sub> V <sub>rrm</sub>	200 400 600	V
*On-State RMS Current (T <sub>C</sub> = 85°C) Full Cycle Sine Wave 50 to 60 Hz	I <sub>T(RMS)</sub>	4.0	А
*Peak Non–repetitive Surge Current (One Full cycle, 60 Hz, $T_J$ = +110°C)	I <sub>TSM</sub>	30	А
Circuit Fusing Considerations (t = 8.3 ms)	l <sup>2</sup> t	3.7	A <sup>2</sup> s
*Peak Gate Power (Pulse Width $\leq$ 1.0 $\mu s,~T_C$ = 85°C)	P <sub>GM</sub>	10	W
*Average Gate Power (t = 8.3 ms, $T_C = 85^{\circ}C$ )	P <sub>G(AV)</sub>	0.5	W
*Peak Gate Voltage (Pulse Width $\leq$ 1.0 $\mu s,~T_C$ = 85°C)	V <sub>GM</sub>	5.0	V
*Operating Junction Temperature Range	TJ	-40 to +110	°C
*Storage Temperature Range	T <sub>stg</sub>	-40 to +150	°C
Mounting Torque (6-32 Screw) (Note 2)	-	8.0	in. lb.

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

 V<sub>DRM</sub> and V<sub>RRM</sub> for all types can be applied on a continuous basis. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.

Torque rating applies with use of a compression washer. Mounting torque in excess of 6 in. lb. does not appreciably lower case-to-sink thermal resistance. Main terminal 2 and heatsink contact pad are common.

#### THERMAL CHARACTERISTICS

Characteristic		Max	Unit
*Thermal Resistance, Junction-to-Case	$R_{ ext{ heta}JC}$	3.5	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{\thetaJA}$	75	°C/W
Maximum Lead Temperature for Soldering Purposes 1/8" from Case for 10 Seconds	ΤL	260	°C


\*Indicates JEDEC Registered Data.

ELECTRICAL CHARACTERISTICS (T <sub>C</sub> = 25°C unless otherwise noted; Electricals apply in both direction	ections)
---	----------

Characteristic	Symbol	Min	Тур	Max	Unit	
DFF CHARACTERISTICS						
*Peak Repetitive Blocking Current (V <sub>D</sub> = Rated V <sub>DRM</sub> , V <sub>RRM;</sub> Gate Open)	T <sub>J</sub> = 25°C T <sub>J</sub> = 110°C	I <sub>DRM,</sub> I <sub>RRM</sub>			10 2	μA mA
ON CHARACTERISTICS						
*Peak On-State Voltage (Note 3) ( $I_{TM} = \pm 6.0 \text{ A Peak}$ )		V <sub>TM</sub>	-	-	2	V
*Gate Trigger Voltage (Continuous DC), All Quadrants (Main Terminal Voltage = 12 Vdc, $R_L$ = 100 $\Omega$ , $T_J$ = -4	40°C)	V <sub>GT</sub>	_	1.4	2.5	V
Gate Non–Trigger Voltage, All Quadrants (Main Terminal Voltage = 12 Vdc, $R_L$ = 100 $\Omega$ , $T_J$ = 110°C)		V <sub>GD</sub>	0.2	-	_	V
*Holding Current (Main Terminal Voltage = 12 Vdc, Gate Open, Initiating	g Current = $\pm 1$ Adc) T <sub>J</sub> = -40°C T <sub>J</sub> = 25°C	Ι <sub>Η</sub>	-		30 15	mA
Turn-On Time (I <sub>TM</sub> = 14 Adc, I <sub>GT</sub> = 100 mAdc)		t <sub>gt</sub>	-	1.5	-	μs
			QUADRANT (Maximum Value)		)	
	Туре	I <sub>GT</sub> @ Т <sub>Ј</sub>	l mA	ll mA	III mA	IV mA
Gate Trigger Current (Continuous DC)	2N6071A	+25°C	5	5	5	10
(Main Terminal Voltage = 12 Vdc, $R_L = 100 \Omega$ )	2N6073A 2N6075A	-40°C	20	20	20	30
		+25°C	3	3	3	5
	2N6073B 2N6075B	-40°C	15	15	15	20
DYNAMIC CHARACTERISTICS						
Critical Rate of Rise of Commutation Voltage @ V <sub>DRM</sub> , T <sub>J</sub> = 85°C, Gate Open, I <sub>TM</sub> = 5.7 A, Expone Commutating di/dt = 2.0 A/ms	ential Waveform,	dv/dt(c)	-	5	_	V/µs

3. Pulse Test: Pulse Width  $\leq$  2.0 ms, Duty Cycle  $\leq$  2%. \*Indicates JEDEC Registered Data.

#### SAMPLE APPLICATION: TTL-SENSITIVE GATE 4 AMPERE TRIAC TRIGGERS IN MODES II AND III



Trigger devices are recommended for gating on Triacs. They provide:


1. Consistent predictable turn-on points.


2. Simplified circuitry.

3. Fast turn-on time for cooler, more efficient and reliable operation.

### Voltage Current Characteristic of Triacs (Bidirectional Device)

Symbol	Parameter
V <sub>DRM</sub>	Peak Repetitive Forward Off State Voltage
I <sub>DRM</sub>	Peak Forward Blocking Current
V <sub>RRM</sub>	Peak Repetitive Reverse Off State Voltage
I <sub>RRM</sub>	Peak Reverse Blocking Current
V <sub>TM</sub>	Maximum On State Voltage
Ι <sub>Η</sub>	Holding Current






## **Quadrant Definitions for a Triac**

All polarities are referenced to MT1.

With in-phase signals (using standard AC lines) quadrants I and III are used.

SENSITIVE (	GATE LOGIC	REFERENCE
-------------	------------	-----------

IC Logic Functions	Firing Quadrant				
ie Logie Functions	I	II	111	IV	
TTL		2N6071A Series	2N6071A Series		
HTL		2N6071A Series	2N6071A Series		
CMOS (NAND)	2N6071B Series			2N6071B Series	
CMOS (Buffer)		2N6071B Series	2N6071B Series		
Operational Amplifier	2N6071A Series			2N6071A Series	
Zero Voltage Switch		2N6071A Series	2N6071A Series		






Figure 10. Thermal Response


#### ORDERING INFORMATION


Device	Package	Shipping <sup>†</sup>
2N6071A	TO-225	
2N6071AG	TO–225 (Pb–Free)	
2N6071B	TO-225	7
2N6071BG	TO–225 (Pb–Free)	
2N6071BT	TO-225	
2N6071BTG	TO–225 (Pb–Free)	
2N6073A	TO-225	7
2N6073AG	TO–225 (Pb–Free)	500 Units / Box
2N6073B	TO-225	7
2N6073BG	TO–225 (Pb–Free)	
2N6075A	TO-225	7
2N6075AG	TO–225 (Pb–Free)	1
2N6075B	TO-225	7
2N6075BG	TO-225 (Pb-Free)	1

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS

**TO-225** CASE 77-09 ISSUE Z





 CONTROLLING DIMENSION: INCH.
077-01 THRU -08 OBSOLETE, NEW STANDARD 077-09.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.425	0.435	10.80	11.04
В	0.295	0.305	7.50	7.74
С	0.095	0.105	2.42	2.66
D	0.020	0.026	0.51	0.66
F	0.115	0.130	2.93	3.30
G	0.094 BSC		2.39 BSC	
Н	0.050	0.095	1.27	2.41
J	0.015	0.025	0.39	0.63
Κ	0.575	0.655	14.61	16.63
Μ	5°.	ТҮР	5°	TYP
Q	0.148	0.158	3.76	4.01
R	0.045	0.065	1.15	1.65
S	0.025	0.035	0.64	0.88
U	0.145	0.155	3.69	3.93
V	0.040		1.02	

STYLE 5: PIN 1. MT 1 2. MT 2 3. GATE

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other application in which the failure of the SCILLC product create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use persons, and reasonable attorney fees andising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use persons and sensing out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized to applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 61312, Phoenix, Arizona 85082–1312 USA Phone: 480–829–7710 or 800–344–3860 Toll Free USA/Canada Fax: 480–829–7709 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center 2–9–1 Kamimeguro, Meguro–ku, Tokyo, Japan 153–0051 Phone: 81–3–5773–3850 ON Semiconductor Website: http://onsemi.com

Order Literature: http://www.onsemi.com/litorder

For additional information, please contact your local Sales Representative.