

# LM301A, LM201A, LM201AV

## Non Compensated Single Operational Amplifiers

A general purpose operational amplifier that allows the user to choose the compensation capacitor best suited to his needs. With proper compensation, summing amplifier slew rates to 10 V/ $\mu$ s can be obtained.

### Features

- Low Input Offset Current: 20 nA Maximum Over Temperature Range
- External Frequency Compensation for Flexibility
- Class AB Output Provides Excellent Linearity
- Output Short Circuit Protection
- Guaranteed Drift Characteristics
- Pb-Free Packages are Available





Figure 1. Standard Compensation and Offset Balancing Circuit




(Pins Not Shown Are Not Connected)

Figure 2. Double-Ended Limit Detector




ON Semiconductor®


### MARKING DIAGRAMS



PDIP-8  
N SUFFIX  
CASE 626



SOIC-8  
D SUFFIX  
CASE 751




■ = Pb-Free Package

▪ = Pb-Free Package

x = 2 or 3  
A = Assembly Location  
WL, L = Wafer Lot  
YY, Y = Year  
WW, W = Work Week  
G = Pb-Free Package  
■ = Pb-Free Package

### PIN CONNECTIONS



### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

# LM301A, LM201A, LM201AV




Figure 3. Representative Circuit Schematic

## ORDERING INFORMATION

Device	Package	Shipping <sup>†</sup>
LM301AD	SOIC-8	98 Units/Rail
LM301ADG	SOIC-8 (Pb-Free)	98 Units/Rail
LM301ADR2	SOIC-8	2500 Tape & Reel
LM301ADR2G	SOIC-8 (Pb-Free)	2500 Tape & Reel
LM301AN	PDIP-8	50 Units/Rail
LM301ANG	PDIP-8 (Pb-Free)	50 Units/Rail
LM201AD	SOIC-8	98 Units/Rail
LM201ADG	SOIC-8 (Pb-Free)	98 Units/Rail
LM201ADR2	SOIC-8	2500 Tape & Reel
LM201ADR2G	SOIC-8 (Pb-Free)	2500 Tape & Reel
LM201AN	PDIP-8	50 Units/Rail
LM201ANG	PDIP-8 (Pb-Free)	50 Units/Rail
LM201AVDR2	SOIC-8	2500 Tape & Reel
LM201AVDR2G	SOIC-8 (Pb-Free)	2500 Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

# LM301A, LM201A, LM201AV

## MAXIMUM RATINGS

Rating	Symbol	Value			Unit
		LM201A	LM201AV	LM301A	
Power Supply Voltage	$V_{CC}, V_{EE}$	±22	±22	±18	Vdc
Input Differential Voltage	$V_{ID}$	–	±30	–	V
Input Common Mode Range (Note 1)	$V_{ICR}$	–	±15	–	V
Output Short Circuit Duration	$t_{SC}$	–	Continuous	–	
Power Dissipation (Package Limitation)	$P_D$				
Plastic Dual-In-Line Package		625	625	625	mW
Derate above $T_A = +25^\circ C$		5.0	5.0	5.0	mW/mW°C
Operating Ambient Temperature Range	$T_A$	–25 to +85	–40 to +105	0 to +70	°C
Storage Temperature Range	$T_{STG}$	–65 to +150	–	–	°C

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

**ELECTRICAL CHARACTERISTICS** ( $T_A = +25^\circ C$ , unless otherwise noted.) Unless otherwise specified, these specifications apply for supply voltages from ±5.0 V to ±20 V for the LM201A and LM201AV, and from ±5.0 V to ±15 V for the LM301A.

Characteristic	Symbol	LM201A / LM201AV			LM301A			Unit
		Min	Typ	Max	Min	Typ	Max	
Input Offset Voltage ( $R_S \leq 50 \text{ k}\Omega$ )	$V_{IO}$	–	0.7	2.0	–	2.0	7.5	mV
Input Offset Current	$I_{IO}$	–	1.5	10	–	3.0	50	nA
Input Bias Current	$I_{IB}$	–	30	75	–	70	250	nA
Input Resistance	$r_i$	1.5	4.0	–	0.5	2.0	–	MΩ
Supply Current $V_{CC}/V_{EE} = \pm 20 \text{ V}$ $V_{CC}/V_{EE} = \pm 15 \text{ V}$	$I_{CC}, I_{EE}$	–	1.8	3.0	–	–	–	mA
Large Signal Voltage Gain ( $V_{CC}/V_{EE} = \pm 15 \text{ V}$ , $V_O = \pm 10 \text{ V}$ , $R_L > 2.0 \text{ k}\Omega$ )	$A_V$	50	160	–	25	160	–	V/mV

The following specifications apply over the operating temperature range.

Input Offset Voltage ( $R_S \leq 50 \text{ k}\Omega$ )	$V_{IO}$	–	–	3.0	–	–	10	mV
Input Offset Current	$I_{IO}$	–	–	20	–	–	70	nA
Avg Temperature Coefficient of Input Offset Voltage (Note 2) $T_A(\min) \leq T_A \leq T_A(\max)$	$\Delta V_{IO}/\Delta T$	–	3.0	15	–	6.0	30	µV/°C
Avg Temperature Coefficient of Input Offset Current (Note 2) $+25^\circ C \leq T_A \leq T_A(\max)$ $T_A(\min) \leq T_A \leq 25^\circ C$	$\Delta I_{IO}/\Delta T$	–	0.01 0.02	0.1 0.2	–	0.01 0.02	0.3 0.6	nA/°C
Input Bias Current	$I_{IB}$	–	–	100	–	–	300	nA
Large Signal Voltage Gain ( $V_{CC}/V_{EE} = \pm 15 \text{ V}$ , $V_O = \pm 10 \text{ V}$ , $R_L > 2.0 \text{ k}\Omega$ )	$A_{VOL}$	25	–	–	15	–	–	V/mV
Input Voltage Range $V_{CC}/V_{EE} = \pm 20 \text{ V}$ $V_{CC}/V_{EE} = \pm 15 \text{ V}$	$V_{ICR}$	–15 –	–	+15 –	–12	–	–	V
Common Mode Rejection ( $R_S \leq 50 \text{ k}\Omega$ )	CMR	80	96	–	70	90	–	dB
Supply Voltage Rejection ( $R_S \leq 50 \text{ k}\Omega$ )	PSR	80	96	–	70	96	–	dB
Output Voltage Swing ( $V_{CC}/V_{EE} = \pm 15 \text{ V}$ , $R_L = \pm 10 \text{ k}\Omega$ , $R_L > 2.0 \text{ k}\Omega$ )	$V_O$	±12 ±10	±14 ±13	–	±12 ±10	±14 ±13	–	V
Supply Currents ( $T_A = T_A(\max)$ , $V_{CC}/V_{EE} = \pm 20 \text{ V}$ )	$I_{CC}, I_{EE}$	–	1.2	2.5	–	–	–	mA


1. For supply voltages less than ±15 V, the absolute maximum input voltage is equal to the supply voltage.

2. Guaranteed by design.

# LM301A, LM201A, LM201AV

## PACKAGE DIMENSIONS

**PDIP-8  
N SUFFIX  
CASE 626-05  
ISSUE L**



### NOTES:

1. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
2. PACKAGE CONTOUR OPTIONAL (ROUND OR SQUARE CORNERS).
3. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	9.40	10.16	0.370	0.400
B	6.10	6.60	0.240	0.260
C	3.94	4.45	0.155	0.175
D	0.38	0.51	0.015	0.020
F	1.02	1.78	0.040	0.070
G	2.54 BSC		0.100 BSC	
H	0.76	1.27	0.030	0.050
J	0.20	0.30	0.008	0.012
K	2.92	3.43	0.115	0.135
L	7.62 BSC		0.300 BSC	
M	---	10°	---	10°
N	0.76	1.01	0.030	0.040

