

650085-000 Product Details

Detailed product features are not currently available online.

Product features can often be found by referring to the available documents. [Contact us](#) for information about this product.

No Image Available

D-436-61

 Always EU RoHS/ELV Compliant (Statement of Compliance)

650085-000

TE Internal Number: 650085-000

 Active

Documentation & Additional Information

Product Drawings:

- [Stub Splice Sealing System Multi-Wire](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available


CAD Files:

- None Available

Related Products:

- [Tooling](#)

SPECIFICATION CONTROL DRAWING



MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene flouride.
2. MELTABLE SEALING RINGS: Modified thermoplastic.
3. SEAMLESS STUB SPLICER: Base Metal: Copper Alloy 101 or 102 per ASTM B-75.
Plating: Tin per MIL-T-10727, Type 1.
Color code: See table below.

Dimensions of Stub Splicer:

Part Name	Prod. Rev.	CMA Range	I.D.	O.D.	Weight Max.	Color Code
D-436-60	A	779 - 2680	1.75 (0.069)	2.68 (0.106)	1.65 lbs/Mpc	Blue
			1.63 (0.064)	2.64 (0.101)		
D-436-61	A	1900 - 6755	2.60 (0.102)	3.89 (0.153)	2.15 lbs/Mpc	Yellow
			2.46 (0.097)	3.73 (0.147)		

APPLICATION

1. These parts are designed to provide an immersion resistant stub splice in wires having insulations rated for at least 135°C.
Wire accommodation: Jacket O.D. – 2.03 (0.080) max

WIRE GAUGE	CMA	NUMBER	
		D-436-60	D-436-61
16	2426	---	2
18	1900	---	2 - 3
20	1216	2	2 - 5
22	754	2 - 3	3 - 8
24	475	2 - 5	4 - 10
26	304	3 - 8	9 - 10

2. Parts will meet performance requirements of MIL-S-81824/1.
3. Recovered dimensions of Insulation Sleeve: I.D – 3.18 (0.125) max
Wall – 0.33 (0.013) min

tyco Electronics		Tyco Electronics Corporation 305 Constitution Drive Menlo Park, CA 94025, USA		Raychem Products		TITLE: STUB SPLICE SEALING SYSTEM MULTI-WIRE	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.				DOCUMENT NO.: D-436-60/-61			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		DATE: 05-Dec.-00		DOC ISSUE: 1	
DRAWN BY: M. FORONDA	REPLACES: N/A	DCR NUMBER: D001301	PROD. REV. SEE TABLE	SCALE: None	SIZE: A	SHEET: 1 of 1	

If this document is printed it becomes uncontrolled. Check for the latest revision.