

CB5368-000 Product Details



CB5368-000
(SST-48-15/226)

TE Internal Number: CB5368-000



Heat Shrink Tubing

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = SST/SST-FR
- Product Source = U.K., U.S.
- Semirigid
- Heavy Wall Style

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • RAYCHEM_TUBING_CATALOG_PRODUCTS_S-Z (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Heat Shrinkable Tubing • Color = Black • Sealant = With <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Product Source = U.K., U.S. • Recovered ID, Max. (mm [in]) = 12.70 [0.500] • Product Use = Wet or Underground Conditions <p>Dimensions:</p> <ul style="list-style-type: none"> • Expanded ID, Min. (mm [in]) = 38.10 [1.500] • Cut Length (mm [in]) = 1219.20 [48.000] <p>Body Features:</p> <ul style="list-style-type: none"> • Product Name = SST/SST-FR • Pliancy = Semirigid • Wall Style = Heavy • Wall Type = Single • Material = Polyolefin • Shrink Ratio = 3:1 • Fluid Type = De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Turbine Fuel • Resistant To = Abrasion, Fluids, Moisture • Wall Thickness - Full Recovery (Nominal) (mm [in]) = 3.56 [0.140] <p>Housing Features:</p> <ul style="list-style-type: none"> • Material Systems = No 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • Government/Industry Qualification = No • Flammability Rating Type = Non-Flame-Retardant • UL Rating = None • CSA Certified = No • Approved Standards = ABS, DNV, Lloyd's • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Environmental:</p> <ul style="list-style-type: none"> • Fluid Resistance = Moisture • Operating Temperature (°C) = -55 - +90 <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Full Recovery Temperature (°C) = 121 • Shrink Temperature, Min. (°C) = 90 • High Temperature Compatible = No <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Aerospace, Commercial Electronics, Industrial, Marine, Military, Rail • Emission Free = No <p>Packaging Features:</p> <ul style="list-style-type: none"> • Packaging Method = Piece <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem