

NOT for Patient-Care Vicinity – UL 1363 Medical-Grade Power Strip with 4 Hospital-Grade Outlets, 15 ft. Cord

MODEL NUMBER: **PS-415-HG**



Description

The PS-415-HG Medical-Grade Power Strip supplies power outside of patient-care vicinities, such as administrative areas or in resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. Compliant with UL 1363 specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

A built-in resettable 15A circuit breaker controls power to all outlets and protects the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The 15 ft. cord provides ample reach to a power source.

Keyhole mounting tabs and flanges make installing this power strip easy. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

Features

Power Distribution Outside of Patient-Care Vicinities

- Ideal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes
- 120V, 50/60 Hz power strip complies with UL 1363 specifications

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- Rugged, all-metal housing for long life in demanding environments

Highlights

- Approved for use outside of patient-care vicinities
- Complies with UL 1363 specifications
- 15 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Features 4 NEMA 5-15R-HG hospital-grade outlets
- Easy to mount on a variety of surfaces

Package Includes

- PS-415-HG UL 1363 Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 15 ft. Cord
- Owner's Manual



Premium Safety Features

- Resettable 15A circuit breaker protects against dangerous overloads
- Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box

- Built-in keyhole mounting tabs and flanges make the PS-415-HG easy to install on a variety of surfaces

Specifications

MODEL TEXT	
Key Benefit	Medical-grade power strip with long 15 ft. cord provides versatile power distribution outside of patient-care vicinities.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Outlet Orientation	Single row of 4
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Audible Alarm	No power switch
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 8.65 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 21.9 x 6.4
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>