

## 1.8kW Single-Phase 120V Basic PDU, 13 NEMA 5-15R Outlets, NEMA 5-15P Input, 15 ft. Cord, 1U Rack-Mount

MODEL NUMBER: PDU1215



### Highlights

- NEMA 5-15P input with 15 ft. (4.5 m) cord
- 13 NEMA 5-15R outlets—12 rear and 1 front
- Switchless design prevents accidental shutdown
- Reversible all-metal housing
- Installs in rack, on wall or under counter

### Package Includes

- PDU1215 1.8kW Single-Phase 120V Basic PDU
- Mounting hardware
- Owner's manual

### Description

The PDU1215 1.8kW Single-Phase 120V Basic PDU is the perfect no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Perfectly suited for high-density IT environments, the PDU1215 features a single breakered load bank with 13 NEMA 5-15R outlets—12 in the rear and one in front. The NEMA 5-15P input plug with long 15-foot (4.5 m) cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. A 15A circuit breaker protects connected equipment from dangerous overloads. The reversible all-metal housing mounts in 1U of space in EIA-standard 19-inch racks, as well as on a wall or workbench or under a counter. With a compatible rack and Tripp Lite's [PDU5IDEBRKT](#) accessory (sold separately), you can adapt the PDU1215 for vertical 0U rack-mounting.

### Features

#### Reliable Single-Phase Power Distribution

- Ideal no-frills PDU for networking, telecom, security, audio/video and sound reinforcement applications
- 13 NEMA 5-15R outlets in one breakered load bank
- 15A circuit breaker protects outlets against overloads
- NEMA 5-15P input plug with 15 ft. cord
- Rear-panel grounding lug

#### Switchless Design

- Prevents accidental shutdowns and costly downtime



#### Versatile Installation Options

- Mounts horizontally in 1U of EIA-standard 19 in. 2- and 4-post racks
- Reversible all-metal housing faces front or rear in rack
- Ready for toolless 0U vertical installation with optional PDUSIDEBRKT (sold separately)
- Also mounts on wall, workbench or under a counter

## Specifications

MODEL TEXT	
Key Benefit	Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Ideal for networking, telecom, security, audio/video and sound reinforcement applications.
OVERVIEW	
PDU Type	Basic
OUTPUT	
Output Capacity Details	1.9kW (127V), 1.8kW (120V), 1.5kW (100V) / 15A total capacity
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(13) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A breaker
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Minimum Required Rack Depth (inches)	7.5
Minimum Required Rack Depth (cm)	19.1
Shipping Dimensions (hwd / in.)	2.2 x 20.4 x 9.3
Shipping Dimensions (hwd / cm)	5.6 x 51.8 x 23.6
Shipping Weight (lbs.)	5.2
Shipping Weight (kg)	2.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Dimensions (hwd / cm)	4.44 x 44.5 x 11.4
Unit Weight (lbs.)	4.9
Unit Weight (kg)	2.2
Material of Construction	Metal
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount and undercounter installation supported
PDU Form Factor	1U; Horizontal
Outlets Measurement (Center to Center)	30.2mm
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Back panel grounding lug
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA), CSA-C22.2 (Canada)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>