



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

14-Outlet Economy Network Server Surge Protector, 1U Rack-Mount, 15-ft. Cord, 3000 Joules

MODEL NUMBER: **DRS-1215**



Highlights

- 14 outlets / 15-ft. cord
- 3000 joule rating
- Adjustable rackmount hardware

Package Includes

- DRS-1215 Surge Suppressor
- Warranty information
- Instruction manual

Description

Tripp Lite's DRS-1215 offers surge and noise suppression in a versatile all-metal multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch EIA standard rack. Includes 14 outlets (6 front/8 rear), 15 ft AC power cord and guarded power switch to reduce the risk of accidental shutoff. Diagnostic LED indicates surge protection status.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 14 NEMA5-15R (6 front & 8 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3000 joules

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- 3000 joules AC surge suppression with EMI/RFI filtering
- 14 NEMA 5-15R output receptacles (6 front/8 rear)
- 15 foot AC cord with NEMA 5-15P straight-in plug connection
- Diagnostic LED confirms suppressor operation
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120
Maximum Surge Amps	120000
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	
Switches	Power switch controls power to all outlets
Diagnostic LED Details	Green - Protection Present
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3000
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
EMI / RFI Filtering	40-80 dB
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 9.25
Shipping Dimensions (hwd / cm)	5.72 x 52.07 x 23.50
Shipping Weight (lbs.)	5.5
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 10.16
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Metal
Included Mounting Accessories	Included mounting flanges are pre-installed for 1U rackmount installation and can be re-configured to support a variety of mounting options
Housing Color	Black
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, 0U vertical rackmount, wallmount and under-counter mounting supported - detachable flanges can be re-configured to support a variety of additional mounting options
Outlets Measurement (Center to Center)	Distance between front outlets = 38.9mm; Distance between rear outlets = 38.9mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>