

Data Sheet

DM-II Plus Power Quality Recorder

Amprobe's DM-II PLUS is a full-featured three phase power quality recorder to maintain, diagnose and troubleshoot electrical systems. It measures and records a broad spectrum of power quality parameters. Easy to use, it's capable of measuring and recording voltage, current, voltage anomalies (sags or surges), harmonics, energy and power (active, reactive and apparent), power factor (true and displacement), and frequency. This unique product comes as a complete kit with current transducers and an increased memory size for data storage, larger display size, and real-time downloading using Amprobe's unique Download Suite software.

- AC Current up to 1000A, AC Voltage, Active, Reactive and Apparent Power, Energy, Peak Demand & Power Factor
- All readings are True RMS
- 5 built-in selectable languages: English, French, Italian, German and Spanish
- User selectable rates allow recording from one hour to several months
- Works with single & three phase systems (Y & delta)
- Readings and charts can be viewed on the DM-II LCD screen or downloaded to a PC
- Capable of recording all parameters (single or three phase) simultaneously
- Optional transducers available for 100A and 3000A (flexible) current capability.



No hassle warranty

No waiting.

No shipping charges.

Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

NO HASSLE

Amprobe® Test Tools



DM-II Plus Power Quality Recorder

Data Sheet

General Specifications

Mechanical Features			
Dimensions:	444.5(L) x 273.05(La) x 190.5(H) mm		
	17.50"(L) x 10.75" (La) x 7.50"(H)		
Weight:	11.5 Lb (5.2kg)		
Internal power supply:	6 batteries 1.5V D size NEDA 13A, IEC L20R		
Battery Life:	22 hours		
External power supply	Use only Amprobe power supply Adapter code DMT-EXTPS.		
Display:	dot matrix with backlight		
resolution	128 x 128 dots (16384 dots)		
dot size	0.5mm x 0.5mm		
visible area	73mm x 73mm (2.9" x 2.9")		
No. of samples per period	128		
Clamp:			
Opening:	53 mm (2.15")		
Maximum diameter of the cable:	50 mm (2.00″)		
Reference temperature:	23°C ± 1°C (73°F ± 2°F)		
Operating temperature:	0°C to 50 °C (32°F to 122°F)		
Relative humidity:	<70%		
Storage temperature:	-10°C to 60 °C (14°F to 140°F)		
Storage humidity:	<80%		
Location:	Indoor operation, < 2000 m		
EMC/EMI/ESD	EN61326-1:2006		
Safety			
The instrument complies to the standards: EN 61010-1 :2002			
Insulation:	Class 2 / Pollution Degree 2		
Over-voltage category:	CAT III 370V~ (Phase-Earth)		
	CAT III 635V~ (Phase-Phase)		
Clamps:			
Phase Sequence Detection:	EN 61557-7:2003		

Specifications Accuracy 73°F \pm 2°F (23°C \pm 1°C) with relative humidity < 75%

Voltage measureme	ent (Autoranging)			
Range	Accuracy		Resolution	Input impedance
15-370V	±(0.5% + 2 digit)		0.2V	300k Ω (phase-neutral)
310-635V	±(0.5% + 2 digit)		0.4V	600k Ω (phase-phase)
Voltage Anomalies	Detection (Manual Selection	on of Range)		
Voltage				
Range	Accuracy		Resolution	Input impedance
15-370V	±(0.5% + 2 digit)		0.2V	300k Ω (phase-neutral)
30-635V	±(0.5% + 2 digit)		0.4V	600kΩ (phase-phase)
Current measureme	ent (DM-II Plus only)			
Range	Accuracy	Resolution	Input impedance	Protection against overloads
0.005-0.26V	±(0.5%+2digit)	0.0001V	100kΩ 5V	0.26-1V 0.0004V
Current measureme	ent (Using DM-CT-HTA)			
Range	Accuracy	Resolution	Protection against overloads	
5 to 1000 A	±(1.5% of range)	0.1 A	600 V	
Minimal Current meas	surable is equal to 1.5% of Cla	amp Full Scale		

Amprobe® Test Tools



DM-II Plus Power Quality Recorder

Specifications, cont.

Current measurement (Using AM-FLEX 33)

Current measurement				
Range		solution Protection again	nst overloads	
15 to 3000 A		I A 600 V		
	able is equal to 1.5% of Clamp Full			
	(cos : 0.5c[positive] – 0.5i[negati			
Value	Ranges	Accuracy	Resolution	
Active power	0 – 999.9W	±(1.5% + 2 digit)	0.1W	
	1kW – 999.9kW	±(1.5% + 2 digit)	0.1kW	
	1MW – 999.9MW	±(1.5% + 2 digit)	0.1MW	
Reactive power	0 – 999.9VAR	±(1.5% + 2 digit)	0.1VAR	
	1kVAR – 999.9kVAR	±(1.5% + 2 digit)	0.1kVAR	
	1MVAR – 999.9MVAR	±(1.5% + 2 digit)	0.1MVAR	
Apparent power	0 – 999.9VA	±(1.5% + 2 digit)	0.1VA	
	1kVA – 999.9kVA	±(1.5% + 2 digit)	0.1kVA	
	1MVA – 999.9MVA	±(1.5% + 2 digit)	0.1MVA	
Active energy	0 – 999.9Wh	±(1.5% + 2 digit)	0.1Wh	
	1kWh – 999.9kWh	±(1.5% + 2 digit)	0.1kWh	
	1MWh – 999.9MWh	±(1.5% + 2 digit)	0.1MWh	
Reactive energy	0 – 999.9VARh	±(1.5% + 2 digit)	0.1VARh	
	1kVARh – 999.9kVARh	±(1.5% + 2 digit)	0.1kVARh	
	1MVARh – 999.9MVAR	h ±(1.5% + 2 digit)	0.1MVARh	
$\textbf{Cos} \ \phi \ \textbf{measurement}$				
Cos φ	Resolution	Resolution Accuracy (expressed in degrees)		
0 to 0.20	0.01	0.6		
0.21 to 0.50	0.01	0.7		
0.51 to 0.80	0.01	1		
Measurement of Har	monics			
Voltage				
Range	Accuracy	Resolution		
DC – 25h	±(5.0% + 2 digit)	0.1V	0.1V	
26h – 33h	±(10.0% + 2 digit)	0.1V	0.1V	
34h – 49h	±(15.0% + 2 digit)	0.1V	0.1V	
The voltage harmonics	will be null under the following the	reshold:		
- DC: if <1V or <2% of 1	st harmonic			
- 1st harmonic: if <2V				
- 2nd to 49th: if <1V or	<2% 1st harmonic			
Current				
Range	Accuracy	Resolution		
DC – 25h	±(5.0% + 2 digit)	0.1A		
26h – 33h	±(10.0% + 2 digit)	0.1A		
34h – 49h	±(15.0% + 2 digit)	0.1A		
The current harmonics	will be null under the following thr	eshold:		
	nonic or < 0,2% of clamp full scale			
- 1st harmonic: if < 0.2%	•			
	harmonic or < 0.2% of clamp full s	cale		
	the DC component will be ignored			
Frequency Measurem				
Instrument set to 50Hz				
Range	Resolution	Accuracy		
47 to 53	0.1Hz	±(1.0% + 1 c	digit)	
Instrument set to 60Hz			-	
Range	Resolution	Accuracy		
57 to 63.6	0.1Hz		±(1.0% + 1 digit)	
			-	

Data Sheet



DM-II Plus Power Quality Recorder

Data Sheet

Included Accessories

DMT-EXTPS DM-CT-HT KITENERGY3

Download Suite 2.2

External power supply 12VDC (code 1 pcs) 3 clamp meters 1000A/1V 4 cables and alligators for voltage measurement 1 Amprobe Custom Software CD Serial Cable

Optional Accessories

AM-FLEX33 DM-CT-100

C232NG1

Flexible current transducer, 3000 A Current transducer, 100A

