













- Impact resistant 10J BS EN 60068-2-75: 1997)
- Weather sealed for outdoor use
- Clear, scratch resistant, anti-reflective display window
- Responsive menu navigation and option select keys
- Under-panel fixing through panel thickness of up to 2mm
- · Supplied complete with panel gasket

- Resistant to petrochemicals and most commonly used cleaning agents
- -20°C (dry) to +60°C (bezel only display temp range specified according to application)
- Accomodates most LCDs with mounting centers at 93 x 55mm or 89.9 x 48.8mm
- Available with or without optional 122 x 32 dot graphic LCD or 4 x 20 character LCD























5000 Series - Toughened Display Bezel

Rear View (No LCD)




WINDOW VIEW AREA IS 76 mm x 25 mm LCD MOUNTING CENTRES AT 93 mm x 55 mm

Overall Dimensions



Host Panel Cutout



Recommended panel material 1.6 or 2.0mm stainless steel. Tolerances \pm 0.5mm



Matrix Keypad Connections

Contact Connections (viewed from rear of keypad)

PINS									
PIN NO.	9	8	7	6	5	4	3	2	1

Contact Matrix

PINS	ROW / COLUMN
7	C1
6	C2
5	C3
3	R1

Unit with LCD fitted



Position 1	Position 2	Position 3		
R1C1	R1C2	R1C3		

Installation

weld stud

- 1. Prepare host panel and connection cable(s). For keypad use Molex 2695 Connector 5 way (PN22-01-2051) or 9 way (PN 22-01-2091). For LCD use PN 22-01-2161.
- 2. Fit the supplied gasket over the 4 weld studs on the rear of the host panel.
- 3. Slide the display bezel over the studs and secure with M3 Nyloc Nuts or similar.

Specifications

Responsive menu navigation and option select keys

Matrix Output to 0.1" square pins compatible with Molex KK Housing

Overall Size 110 mm wide x 88 mm high

Optional backlit 4 line x 20 character LCD fitted with a single row of 16 0.1" square pins LCD Operating Voltage +5V to +9V (see note *)

Powertips PC2004-A-LRU-H

Panel Mount Gasket included

Responsive key action

travel 1.5 mm (nominal)

force 130 gm (nominal)

Panel Cutout 96 mm x 81 mm

-20°C to +60°C Operating Temp

Switch Rating 24 V dc (Max), 50 mA (Max)

Contact Resistance 100 Ohms (Max)

Ordering Details [x] denotes packaging variant

Stock No. 5001-20010[x] Display Bezel 3 Key Display Bezel 3 Key 5001-20020[x] with 4 x 20 character display

Note*: LCD Rating - Temperature Compensation

An LCD operating voltage varies at different temperatures. The operating voltage must rise as temperature lowers or the contrast will degrade. Conversely, the operating voltage must fall as the temperature rises or the contrast will degrade. A temperature compensation circuit is required to control the input voltage as the temperature changes.

For Connection Information for LCD see: Powertip PC 2004-A Datasheet for 4 x 20 Character LCD

> Whilst every effort is made to ensure details are correct at time of print, specifications are subject to change without notice.



500-xx-08KT Rev 2

Oct 2007





14 Bentinck Court Bentinck Road West Drayton Middlesex UB7 7RQ

Storm Interface 600 Enterprise Drive Oak Brook

Illinois 60523 USA

Tel: +44 (0)1895 431421 Fax: +44 (0)1895 431132 Email: sales@storm-interface.com

www.storm-interface.com

Storm Interface products include technology protected by international patents and design registration. All rights reserved.