## **3M** United States

#### 3M Worldwide : United States : Electronics Manufacturing

- Solutions for Electronic Specialty Markets (ESM)
  - Product Catalog for Electronic Specialty Markets
    - 3M<sup>™</sup> Electronic
      Specialty Markets New
      Product Releases
    - 3M<sup>™</sup> Abrasives
    - 3M<sup>™</sup> Adhesives,
    - Cleaners & Compounds
    - 3M<sup>™</sup> Breadboards & Test Clips
    - 3M<sup>™</sup> Cable & Assemblies
    - 3M<sup>™</sup> Copper
      Interconnects
    - 3M<sup>™</sup> Fiber Optics
    - 3M<sup>™</sup> Fire Protection
    - 3M<sup>™</sup> Heat Shrink
    - 3M™ Identification Systems
    - 3M<sup>™</sup> Occupational Health & Safety Products
    - 3M<sup>™</sup> Protective Bumpers
    - 3M<sup>™</sup> Reclosable Fasteners
    - 3M<sup>™</sup> Splicing, Terminating & Ducting
    - 3M<sup>™</sup> Static Control
    - 3M<sup>™</sup> Tapes
    - 3M<sup>™</sup> Terminals, Kits & Tools
    - 3M<sup>™</sup> Vacuums & Accessories
    - 3M<sup>™</sup> Warehousing & Packaging Supplies
    - 3M<sup>™</sup> Wire Connectors

#### other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Product Catalog for Electronic Specialty Markets > 3M<sup>™</sup> Wire Connectors > 3M<sup>™</sup> Spring Connectors and Tools > 3M<sup>™</sup> Wire Connectors T/R+ >

#### Printer-friendly format\_3M<sup>™</sup> Wire Connector T/R+Box, Super Tan, 100 per Box

- Incredible wire range (2 #18 up to 5 #12)
- $\cdot$  One connector replaces 3 (yellow, red & tan) in the majority of all field applications
- · Smooth, comfortable feel
- · Compact size and red miniskirt
- Quick bite spring design
  - · Comfortable wing design for a better grip
  - · Can be installed with 3M<sup>™</sup> WCD-P Wire Connector Drivers

GTIN(UPC/EAN) : 0 00 51128 54454 9 3M Id : 80-6112-3775-3

#### Additional Information

Use a 3M<sup>™</sup> Wire Connector T/R + to electrically connect two or more conductor ends in a pigtail application and insulate the connection.

#### Learn More . . .

Packaging Data T/R+ (Tan/Red) Wire Connector - Data Sheet (PDF 177.5 K)

Please Note: Adobe® Acrobat® Reader is required to view PDF documents.

> Get Acrobat-Adobe Reader

#### Characteristics

UL, CE, and CSA					
Yes					
Tan/Red					
Yes					
600 Volt					
100					
22 to 8					



[click to enlarge]

# **3M** Wire Connector T/R+ (Tan/Red)





Association

Standard NO. 22.2

NO. 188-M1983 3M File NO. LR15503 PASSPORT TO

EUROPEAN UNION

COUNTRIES

Data Sheet

#### Application

Use a  $3M^{T}T/R+$  Wire Connector to electrically connect two or more conductor ends in a pigtail application and insulate the connection.

#### Wire

AWG Range: COPPER conductors only, No. 22 thru No. 8 solid and/or stranded (see wire matrix for specific wire combinations).

METRIC Range: COPPER conductors only, 0,5 mm<sup>2</sup> thru 6,0 mm<sup>2</sup> ridged (solid) and flexible (stranded).

#### Construction

Spring - Spring steel, corrosion resistant coating Insulator: - Flame retardant, polypropylene, tan and thermoplastic elastomer, red


#### Weight

.0068 lbs. (3.1 g)

#### **Performance Test**

The following tests were performed to the specification of UL Standard 486C and CSA Standard C22.2 No. 188-M1983.

Static-Heating	Pass
Secureness	Pass
Pullout	Pass
Dielectric Voltage Withstand	Pass
Secureness-of-Insulation	Pass
Flammability	Pass



#### **Other Tests:**

per MIL-STD-1344A Method 2005.1UV Exposure Pass Per ASTM G-53-77 Salt Spray Pass

#### **Fluid Immersion Test**

Connectors were immersed in the following chemicals for seven days at  $23^{\circ}C\pm 2^{\circ}C$  with no affect on appearance or loss of material strength.

#### Typical Reagents and Materials From ASTM D 543-87 and MIL-STD-1344A


Acetic Acid Acetone Detergent Solution, Heavy Duty Ethyl Alcohol (95%) Ethyl Alcohol (50%) Heptane Hydrogen Peroxide Solution 28% Methyl Alcohol Sodium Hydroxide Solution

#### **Engineering Specification**

Mineral Spirit


Lubricating Oil

3M T/R+ Wire Connector is capable of connecting two or more wires in a pigtail application, in the wire range of No. 22 thru No. 8 AWG solid and/or stranded copper conductors. The connector shall be constructed of an active (live) spring with a corrosion resistant coating. The connector shall be UL LISTED and CSA Certified as a pressure wire connector. The connector shall be voltage rated 600 volts maximum building wire and 1000 volts maximum signs and lighting fixtures (luminaries). The connector shall have a maximum operating temperature of 105°C (221°F).



## **3M** Wire Connector T/R+

### AWG Wire Combinations Copper to Copper Conductors



#### **Installation Instructions**

#### **AWARNING**

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

- **1.** Strip wire insulation 1/2".
- 2. Firmly grasp wires, making sure insulation ends are even and tightly bundled. (Wires may be twisted or untwisted.) Lead stranded wires slightly. Slip the connector over wire tips.
- **3.** Turn connector onto wires in clockwise direction until secure.
- 4. To remove, turn connector counter- clockwise.

#### **Regulatory Agencies**

UL Listed as a Pressure Cable Connector Tested per UL Standard 486C UL File No. E23438 Operating Temperature: 105°C (221°F) Voltage Rating: 600 volts max. building wire; 1000 volts max. signs and fixtures Flammability Rating: UL94 V-2

## CSA Certified-CSA Standard C22.2 No. 0, 188-M1983

CSA File No. LR15503 Operating Temperature: 105°C (221°F) Voltage Rating: 600 volts max. building wire 1000 volts max. signs and luminaires. Flammability Rating: C22.2 No. 0.6 V-2 Operating Temperature: 105°C (221°F) Voltage Rating: 600 volts max. building wire; 1000 volts max. signs and fixtures Flammability Rating: UL94 V-2

#### **Federal Specification W-S-610:**

"Commercial package only"					
Туре	Class	Kind	Style		
1	1	cu	G		

### Metric Wire Combinations

#### **Copper Conductors Only**

Cross Section Capacity			Conductor Combination	าร
Minimum	Maximum	Quantity	Size	Туре
2.0mm <sup>2</sup>	12.5mm <sup>2</sup>	6	0,5mm²	sol/str
		3-6	0,75mm <sup>2</sup>	sol/str
		2-6	1,0mm²	sol/str
		2-6	1,5mm²	sol/str
		2.5	2,5mm²	sol/str
		2.3	4.0 mm <sup>2</sup>	sol/str

Only AWG combinations are UL Listed or CSA Certified.