


ES SERIES

RELAY SOCKETS



DESCRIPTION	8, 11 and 14 Pin Miniature Sockets, DIN Rail Mountable, Finger Safe
ELECTRICAL RATING	• 300 Volts, 10 Amps ; 300 Volts, 12 Amps
CONSTRUCTION	Contacts • Brass, Nickel Plated Screws • M3 Steel, Nickel Plated, Maximum Wire Gauge #14 Molding • Break Resistant Thermoplastic
AGENCY APPROVALS	• UL recognized, File No. E113714 • CSA certified, File No. LR26716 • CE

ORDERING CODE


PART NO.	DESCRIPTION	TERMINAL TYPE
ES15/2N	DPDT, 8 Pin Miniature (Fig. 1)	Box Lug
ES15/3N	3PDT, 11 Pin Miniature (Fig. 2)	Box Lug
ES15/4N	4PDT, 14 Pin Miniature (Fig. 1)	Box Lug

ACCESSORIES

PART NO.	DESCRIPTION (Refer to the accessories pages 25-27)
C-103-PM	Prepunched Aluminum DIN Rail (1 Meter Lengths)
C-104-PM	Prepunched Steel DIN Rail (1 Meter Lengths)
C-105-PM	Prepunched Steel DIN Rail (1 Meter Lengths)
C-106-2PM	Prepunched Steel DIN Rail (2 Meter Lengths)
C-108-PM	Prepunched Raised Aluminum DIN Rail (1 Meter Lengths)
C-108-2PM	Prepunched Raised Aluminum DIN Rail (2 Meter Lengths)
MHO	Hold Down Spring
MS35	Hold Down Spring/Ejector

PLUG-IN INDICATOR AND PROTECTION MODULES

PART NO.	DESCRIPTION
Type 22	Diode for 6-230V DC (+Terminal A1)
Type 42V	Green LED with Diode for 6-24V DC (+ Terminal A1)
Type 42CV	Green LED with Diode for 110-230V DC (+ Terminal A1)
Type 52B	RC Circuit for 6-24V AC
Type 52C	RC Circuit for 110-240V AC
Type 62V	Green LED for 6-24V AC/DC (For DC + Terminal A1)
Type 92V	Green LED for 110-240V AC/DC (For DC + Terminal A1)
Type 62CV	Varistor + Green LED for 6-24V AC/DC (For DC + Terminal A1)
Type 92CV	Varistor + Green LED for 110-240V AC/DC (For DC + Terminal A1)
Type 102	Bypass Resistor 110-240V AC




TERMINAL LOCATION

TOP VIEW

ES15/2N SERIES NOTE:

ES15/2N is the same as ES15/4N but with terminals 2, 3, 6, 7, 10 & 11 omitted



TERMINAL LOCATION

TOP VIEW