

55 Watt 32" Reach Halogen Machine Lamp - Integrated Transformer



- 32" articulated overall reach
- 12 volt integrated transformer
- 55 watt Halogen bulb
- 9.5 ft grounded SJTO cord & plug
- Direct mounting base
- Positive locking swivels
- Instant focusing
- Rubber boot switch on shade

Model: 7750

This rugged, all metal construction, waterproof machine task light provides excellent illumination in tough and wet locations. Engineered to deliver intensified, bright white Halogen light to meet the needs of demanding shop environments, it features safe, low voltage, 55w/12v power. This light meets NEMA Type 4 certification (hose down, icing and gaskets application), which makes it ideal for CNC and EDM wet location machinery, lathes, milling, metal-working and tool manufacturing. Added safety features include a rubber boot switch, sealed from liquids, a 9 ft grounded, oil and water resistant SJTO cord with 3-prong plug, and integrated transformer housed in a liquid tight precision cast zinc base housing. The heavy gauge aluminum shade is precision machined to fit a vented inner chamber which eliminates heat build-up, providing added comfort to the operator while maintaining water tight features. With an overall 32" reach, the articulated swing arm features built-in positive locking zinc cast swivels. 3 year warranty. Made in USA. Available Colors: Gray