3M United States

3M Worldwide : United States : Electronics Manufacturing

- Solutions for Electronic Specialty Markets (ESM)
 - Product Catalog for Electronic Specialty Markets
 - 3M[™] Electronic
 Specialty Markets New
 Product Releases
 - 3M[™] Abrasives
 - 3M[™] Adhesives, Cleaners & Compounds
 - 3M™ Breadboards & Test Clips
 - 3M[™] Cable & Assemblies
 - 3M[™] Copper
 Interconnects
 - 3M[™] Fiber Optics
 - 3M[™] Fire Protection
 - 3M[™] Heat Shrink
 - 3M™ Identification Systems
 - 3M[™] Occupational Health & Safety Products
 - 3M[™] Protective Bumpers
 - 3M[™] Reclosable Fasteners
 - 3M[™] Splicing, Terminating & Ducting
 - 3M[™] Static Control
 - 3M[™] Tapes
 - 3M™ Terminals, Kits & Tools
 - 3M[™] Vacuums & Accessories
 - 3M[™] Warehousing & Packaging Supplies
 - 3M[™] Wire Connectors

• Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

Product Catalog for Electronic Specialty Markets > <u>3M™</u> Terminals, Kits & Tools > Forks > Highland[™] Locking Fork Terminals - Non-Insulated Butted Seam >

Printer-friendly format 3M[™] Highland[™] Non-Insulated Locking Fork LF18-6L, 22-18 AWG

This terminal has a wire range of 22-18 AWG and a stud size of 6. It has case quantities of 500

GTIN(UPC/EAN) : 0 00 54007 70297 9 3M Id : 80-6105-8810-7

Additional Information

The spring-like tongue locks into place around the stud even when the mount screw is not tightened. Extra force is required to remove it from the stud.

Learn More . . .

Packaging Data

Highland Locking Forks - Non-Insulated - Product Selection Guide (PDF 8.0 K)

Highland Terminals LF10-6 thru LF18-8 - Data Sheet (PDF 21.6 K)

Terminal Stud Size Chart - Product Selection Guide (PDF 5.2 K)

Please Note: Adobe® Acrobat® Reader is required to view PDF documents.




Characteristics	
Agency Approvals	UL and CSA
Barrel Style	Butted
China RoHS - Below MCV	Yes
CSA File Number	LR22190
EU RoHS Compliant	Yes
Stud Size	6 American Wire Gauge (AWG)
Terminal Style	Locking
Terminal Type	Fork
UL File Number	E23438

Wire Gauge Range

3M Highland[™] Terminals

LF10-6 thru LF18-8 Locking Fork, Non-Insulated, Butted Seam



Data Sheet

Product Number	Wire Range (AWG)	Stud Size	Max Lock Width	w	С	L	E	Thickness	Barrel Length	Barrel I.D.
LF10-6	12-10	6	0.30	0.28	0.28	0.73	0.53	0.040	0.25	0.135
LF10-8	12-10	8	0.35	0.32	0.28	0.73	0.53	0.040	0.25	0.135
LF10-10	12-10	10	0.36	0.32	0.28	0.73	0.53	0.040	0.25	0.135
LF10-14	12-10	1⁄4	0.48	0.43	0.44	0.94	0.69	0.040	0.25	0.135
LF14-6	16-14	6	0.27	0.25	0.25	0.68	0.50	0.030	0.25	0.090
LF14-8	16-14	8	0.34	0.30	0.25	0.68	0.50	0.030	0.25	0.090
LF14-10	16-14	10	0.35	0.32	0.25	0.68	0.50	0.030	0.25	0.090
LF18-4	22-18	4	0.27	0.25	0.25	0.68	0.50	0.030	0.25	0.070
LF18-6	22-18	6	0.27	0.25	0.25	0.68	0.50	0.030	0.25	0.070
LF18-8	22-18	8	0.34	0.30	0.25	0.68	0.50	0.030	0.25	0.070



UNDERWRITERS LABORATORIES STANDARD NO. UL 486A 3M FILE NO. E23438

Specifications

Wire Size: Barrel Seam: Max. Current: Terminal Material: Plating:



CANADIAN STANDARDS ASSOCIATION STANDARD NO. C22.2 NO. 0. 65 3M FILE NO. LR22190

See Table Above Butted Same as Wire ETP Copper Tin

Installation Information


WARNING


Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end 3/8 inch of wire insulation.

Make the crimp in the proper station of a recommended 3M crimp tool: TH-440, TH-450 (scissor style), or TR-490 (ratchet style) hand tools.





Engineering Specification

Crimp-type terminals shall, electrically and mechnically, connect to a pre-stripped end of a stranded copper wire: and have a flat tongue portion with a central opening for mounting around a screw or stud.

The terminal line shall offer tongue variations in hole (stud) size (6, 8 10, etc.) and configuration (ring, fork, block fork, flanged block fork, locking fork, etc.): and barrel variations in wire (AWG) size (22-18, 16-14, 12-10, etc.) and construction (non-insulated brazed seam, vinyl insulated butted seam, nylon insulated with insulation grip, etc.). The terminal line shall have regulatory agency coverage (UL Listing, CSA Certification). The terminal tongue shall be marked with the wire range and manufacturer's symbol (\uparrow).

The non-insulated, butted seam locking fork terminal shall be tin-plated, annealed copper, with the tongue having a specified stud slot (size 4 thru 1/4 in.) and a butted seam barrel with a beveled I.D. for ease of stranded wire entry, sized for a specified (AWG) wire range (22-18, 16-14, 12-10).

Non-insulated terminals shall be UL Listed and CSA Certified.

3M and Highland are trademarks of 3M

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.

ЗМ

Electrical Products Division 6801 River Place Blvd. Austin, TX 78726-9000 http://www.3M.com/elpd