

3M Worldwide : United States : Government Solutions

Product Catalog for Government Solutions ➤ Emergency Preparedness, Response & Recover ➤ 3.

Emergency Recovery ➤ Restoration & Rebuilding ➤ 3M™ Adhesives ➤ 3M™ Scotch-Weld™ Epoxy

Adhesive DP-270 Black ➤

3M[™] Scotch-Weld[™] Epoxy Potting Compound DP270 Black Duo-Pak, 1.7 fl oz, 12 per case



An electrical grade two-part epoxy for potting and bonding electronic components, and is electrolytically non-corrosive to copper. It has a 1:1 mix ratio and is a non-exotherming, high flow, opaque black product with a 70 minute worklife.

GTIN(UPC/EAN): 0 00 21200 82262 9

3M Id: 62-3266-1435-1

Characteristics

Color Black
Product Form Each
Trademark Name 1 3M

Trademark Name 2 Scotch-Weld

©3M 1995-2006 Legal Information Privacy Policy



3M Worldwide : United States : Government Solutions

Product Catalog for Government Solutions ☐ Emergency Preparedness, Response & Recover ☐ 3.

Emergency Recovery ☐ Restoration & Rebuilding ☐ 3M™ Adhesives ☐ 3M™ Scotch-Weld™ Epoxy

Adhesive DP-270 Black ☐ 3M™ Scotch-Weld™ Epoxy Potting Compound DP270 Black Duo-Pak, 1.7 floz, 12 per case

3M[™] Scotch-Weld[™] Epoxy Potting Compound DP270 Black Duo-Pak, 1.7 fl oz, 12 per case Packaging

3M Id: 62-3266-1435-1

Minimum Order Quantity: 12.0 EACH

Case Quantity: 12.0 EACH

	English	Metric	
Length	6.1 INCH	0.155 MTR	
Width	4.6 INCH	0.118 MTR	
Height	5.3 INCH	0.135 MTR	
Gross Weight	2.1400 LBS	0.9707 KG	

©3M 1995-2006 Legal Information Privacy Policy

3M Scotch-Weld[™] Epoxy Potting Compound/Adhesive DP270 Clear and Black

Technical Data

Product Description

3M™ Scotch-Weld™ Epoxy Potting Compound/Adhesive DP270 (or 3M™ Scotch-Weld™ Epoxy Potting Compound/Adhesive 270 B/A) is a two-part, low viscosity epoxy resin system designed primarily for potting, sealing, and encapsulation of many electronic components and is available in clear or black. Scotch-Weld epoxy potting compound/adhesive DP270 is noncorrosive to copper and offers good thermal shock resistance and excellent retention of electrical insulation properties under high humidity conditions.

Scotch-Weld epoxy potting compound/adhesive DP270 has a work life of approximately 70 minutes, a tack-free time of about 3 hours and is fully cured after 48 hours at 73°F (23°C). This product produces no exotherm in 5-10 gram masses and a very slight exotherm in larger masses.

Scotch-Weld epoxy potting compound/adhesive DP270 is ideal for the potting and encapsulation of many heat sensitive or delicate components such as glass diodes and sensors as well as for transformers, coils, chokes, relays, etc. It is available in the convenient 3MTM EPXTM Applicator System for multi-station usage and in bulk containers for larger volume applications.

Available in bulk containers as Scotch-Weld epoxy potting compound/adhesive 270 B/A.

Features

- Good Thermal Shock Resistance
- Meets UL 94 HB (File No. E61941)
- · Long Worklife

- Excellent Electrical Properties
- Noncorrosive to Copper
- Negligible Exotherm

Typical Uncured Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Color:	Clear or Black			
Base Resin:	Epoxy/amine			
Mix Ratio:	1:1 by volume (1:0.85 B:A by weight)			
Net Weight: Lbs./Gal.	Base 9.6 - 9.8 Accelerator 8.0 - 8.2			
Worklife:	60-70 minutes @ 23°C (73°F)			
Viscosity: @ 23°C (73°F)	Base 7000 - 16,000 cps Accelerator 6000 - 12,000 cps			

$\textbf{Scotch-Weld}^{^{\text{\tiny TM}}}$

Epoxy Potting Compound/Adhesive

DP270 Clear and Black

Typical Cured Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Clear or Black	
Clear 1.656	
.08%	
83	
Approx. 3 hrs. @ 23°C (73°F)	
94 HB (File No. E61941)	
48 hrs. @ 23°C (73°F)	
1% @ 122°C (252°F) 5% @ 175°C (347°F) 10% @ 210°C (410°F)	
80 x 10 ⁻⁶ units/unit/°C 5-30°C range (10-86°F range)	
180 x 10-6 units/unit/°C 60-125°C range (140-257°F)	
43°C (109°F) 49°C (120°F)	
.103 .426 x 10 ³ .177	
Pass 5 Cycles without cracking	
3.5 @ 1 KHz @ 23°C (73°F)	
.018 @ 1 KHz @ 23°C (73°F)	
850 volts/mil	
4.1 x 10 ¹⁴ ohm-cm	
3 x 10 ¹³ ohms 2 x 10 ¹¹ ohms	

$\textbf{Scotch-Weld}^{\text{\tiny TM}}$

Epoxy Potting Compound/Adhesive DP270 Clear and Black

Store product at 60-80°F (16-27°C) for maximum storage life.
These products when stored in original, unopened container have a shelf life of two years for bulk containers and 15 months in duo-pak containers.
Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/adhesives. Address correspondence to: 3M Industrial Adhesives and Tapes Division Building 21-1W-10, 900 Bush Avenue, St. Paul, MN 55144-1000. Our fax number is 651-778-4244. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00
All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.
Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.
Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

Industrial Business Industrial Adhesives and Tapes Division

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.



Material Safety Data Sheet

Copyright, 2008, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: 3M(TM) Scotch-Weld(TM) Epoxy Potting Compound/Adhesive DP-270, Black (Part B)

MANUFACTURER: 3M

DIVISION: Industrial Adhesives and Tapes Division

Document Group: 11-1418-0

Product Use:

Specific Use: base component two part epoxy adhesive

Intended Use: Structural adhesive

SECTION 2: INGREDIENTS

Ingredient	<u>C.A.S. No.</u>	<u>% by Wt</u>
EPOXY RESIN	25068-38-6	90 - 99
HYDROCARBON RESIN	9003-53-6	3 - 7
CARBON BLACK	1333-86-4	0.5 - 1.5

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: black, very mild odor.

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: May cause allergic skin reaction.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

8.2.1 Eye/Face Protection

The following eye protection(s) are recommended: Safety Glasses with side shields, Indirect Vented Goggles.

8.2.2 Skin Protection

Wear appropriate gloves, such as Nomex, when handling this material to prevent thermal burns. Avoid skin contact. Avoid skin contact with hot material. Gloves are not required.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials. Gloves made from the following material(s) are recommended: Polyethylene/Ethylene Vinyl Alcohol.

8.2.3 Respiratory Protection

Avoid breathing of dust created by cutting, sanding, grinding or machining.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half mask R95 particulate respirator, Half mask or full facepiece air-purifying respirator with N100 particulate filters, Half facepiece or fullface air-purifying respirator with P100 particulate filters, Half facepiece or fullface air-purifying respirator with N95 particulate filters. Consult the current 3M Respiratory Selection Guide for additional information or call 1-800-243-4630 for 3M technical assistance.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Wash hands after handling and before eating.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	Authority	<u>Type</u>	<u>Limit</u>	Additional Information
CARBON BLACK	ACGIH	TWA	3.5 mg/m3	Table A4
CARBON BLACK	CMRG	TWA	0.5 mg/m3	
CARBON BLACK	OSHA	TWA	3.5 mg/m3	Table Z-1

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade: black, very mild odor.

General Physical Form: Liquid

Autoignition temperature No Data Available

Flash Point >=370.00 °F [Test Method: Cleveland Open Cup]

Flammable Limits - LEL

Flammable Limits - UEL

Boiling point

Not Applicable

Not Applicable

> 300 °F

Vapor Density Not Applicable

Vapor Pressure <=27 psia [@ 131 °F]

Specific Gravity 1.150 [Ref Std: WATER=1]

MATERIAL SAFETY DATA SHEET 3M(TM) Scotch-Weld(TM) Epoxy Potting Compound/Adhesive DP-270, Black (Part B)

pHMelting point
Not Applicable
No Data Available

Solubility in Water Nil

Evaporation rateNot ApplicableVolatile Organic CompoundsNot ApplicablePercent volatileNot ApplicableVOC Less H2O & Exempt SolventsNot Applicable

Viscosity 13000.0 - 16000.0 centipoise [Details: CONDITIONS: (@ Room

Temperature)]

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid: Strong acids; Strong oxidizing agents; Heat is generated during cure. Do not cure a mass larger than 50 grams in a confined space to prevent a premature reaction (exothem) with production of intense heat and smoke.

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

SubstanceConditionAldehydesDuring CombustionHydrocarbonsDuring CombustionCarbon monoxideDuring CombustionCarbon dioxideDuring CombustionKetonesDuring CombustionToxic Vapor, Gas, ParticulateDuring Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS