3M United States

3M Worldwide : United States : Government Solutions

Product Catalog for Government Solutions □ 3M[™] Government Facilities Products □ General Maintenance □ Adhesives □ 3M[™] Structural Adhesives □ 3M[™] Structural Liquids And Pastes □ 3M[™] Scotch-Weld[™] Two Part Epoxy Adhesives □

3M[™] Scotch-Weld[™] Epoxy Adhesive 2216 B/A Translucent



Long worklife adhesive. Flexible epoxy. Translucent version of 2216 B/A Gray Adhesive.

3M Scotch-Weld[™] Epoxy Adhesive 2216 B/A

Technical Data	
Product Description	3M TM Scotch-Weld TM Epoxy Adhesive 2216 B/A is a flexible, two-part, room temperature curing epoxy with high peel and shear strength. Scotch-Weld epoxy adhesive 2216 B/A is identical to 3M TM Scotch-Weld TM Epoxy Adhesive EC-2216 B/A in chemical composition. Scotch-Weld epoxy adhesive EC-2216 B/A has been labeled, packaged, tested, and certified for aircraft and aerospace applications. Scotch-Weld epoxy adhesive 2216 B/A may be used for aircraft and aerospace applications if proper Certificates of Test have been issued and material meets all aircraft manufacturer's specification requirements.

Typical Uncured	Note: The following technical information and data should be considered representative
Physical Properties	or typical only and should not be used for specification purposes.

Product	3M™ Scotch-Weld™ Epoxy Adhesive					
	2216 B/A Gray		2216 B/A Tan NS		2216 B/A Translucent	
	Base	Accelerator	Base	Accelerator	Base	Accelerator
Color:	White	Gray	White	Tan	Translucent	Amber
Base:	Modified Epoxy	Modified Amine	Modified Epoxy	Modified Amine	Modified Epoxy	Modified Amine
Net Wt.: (Ib/gal)	11.1-11.6	10.5-11.0	11.1-11.6	10.5-11.0	9.4-9.8	8.0-8.5
Viscosity: (cps) (Approx.) Brookfield RVF #7 sp. @ 20 rpm	75,000 - 150,000	40,000 - 80,000	75,000 - 150,000	550,000 - 900,000	11,000 - 15,000	5,000 - 9,000
Mix Ratio: (by weight)	5 parts	7 parts	5 parts	7 parts	1 part	1 part
Mix Ratio: (by volume)	2 parts	3 parts	2 parts	3 parts	1 part	1 part
Work Life: 100 g Mass @ 75°F (24°C)	90 minutes	90 minutes	120 minutes	120 minutes	120 minutes	120 minutes

Features

• Excellent for bonding many metals, woods, plastics, rubbers, and masonry products.

- Base and Accelerator are contrasting colors.
- Good retention of strength after environmental aging.
- Resistant to extreme shock, vibration, and flexing.
- Excellent for cryogenic bonding applications.
- The tan NS Adhesive is non-sag for greater bondline control.
- The translucent can be injected.
- Meets DOD-A-82720.

Scotch-Weld[™] Epoxy Adhesive 2216 B/A

Typical Cured Physical Properties	Product	3M™ Scotch-Weld™ Epoxy Adhesive				
		2216 Gray	2216 Tan NS	2216 Translucent		
	Color	Gray	Tan	Translucent		
	Shore D Hardness ASTM D 2240	50-65	65-70	35-50		
	Time to Handling Strength	8-12 hrs.	8-12 hrs.	12-16 hrs.		

Typical Cured	Product	3M™ Scotch-Weld™ Epox	y Adhesive	
Electrical Properties		2216 Gray	2216 Translucent	
	Arc Resistance	130 seconds		
	Dielectric Strength	408 volts/mil	630 volts/mil	
	Dielectric Constant @ 73°F (23°C)	5.51–Measured @ 1.00 KHz	6.3 @ 1 KHz	
	Dielectric Constant @ 140°F (60°C)	14.17-Measured @ 1.00 KHz	—	
	Dissipation Factor 73°F (23°C)	0.112 Measured @ 1.00 KHz	0.119 @ 1 KHz	
	Dissipation Factor 140°F (60°C)	0.422-Measured @ 1.00 KHz	—	
	Surface Resistivity @ 73°F (23°C)	5.5 x 10 ¹⁶ ohm-@ 500 volts DC	—	
	Volume Resistivity @ 73°F (23°C)	1.9 x 10 ¹² ohm-cm-@ 500 volts DC	3.0 x 10 ¹² ohm-cm @ 500 volts DC	

Typical Cured Thermal Properties	Product	3M™ Scotch-Weld™ Epoxy Adhesive		
		2216 Gray	2216 Translucent	
	Thermal Conductivity	0.228 Btu-ft/ft ² h°F	0.114 Btu-ft/ft ² h°F	
	Coefficient of Thermal Expansion	102 x 10 ⁻⁶ in/in/°C between 0-40°C	81 x 10 ⁻⁶ in/in/°C between -50-0°C	
		134 x 10 ^{.6} in/in/°C between 40-80°C	207 x 10 ⁻⁶ in/in/°C between 60-150°C	

Typical Cured Outgassing Properties	Outgassing Data NASA 1124 Revision 4			
		% TML	% CVCM	% Wtr
	3M [™] Scotch-Weld [™] Epoxy Adhesive 2216 Gray	.77	.04	.23
	Cured in air for 7 days @ 77°F (25°C).			

Handling/Curing Information

Directions for Use

- 1. For high strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user. For suggested surface preparations of common substrates, see the following section on surface preparation.
- 2. These products consist of two parts. Mix thoroughly by weight or volume in the proportions specified on the product label and in the uncured properties section. Mix approximately 15 seconds after a uniform color is obtained.

 $\textbf{Scotch-Weld}^{{}^{\scriptscriptstyle{\mathsf{TM}}}}$ Epoxy Adhesive 2216 B/A

Precautionary Information	Refer to Product Label and Material Safety Data Sheet for Health and Safety Information before using this product.
Product Use	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.
Warranty and Limited Remedy	Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.
Limitation of Liability	Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.
	(ISO 9001:2000)
	This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division



Material Safety Data Sheet

Copyright, 2005, 3M Company. All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

 PRODUCT NAME:
 SCOTCH-WELD (TM) 2216 B/A Part B Translucent Epoxy Adhesive

 MANUFACTURER:
 3M

 DIVISION:
 Industrial Adhesives and Tapes

 ADDRESS:
 3M Center

St. Paul, MN 55144-1000

Issue Date: 03/28/2005 **Supercedes Date:** 08/15/2003

Document Group: 10-3171-5

Product Use:

Specific Use:

base for 2 part adhesive

SECTION 2: INGREDIENTS

Ingredient EPOXY RESIN <u>C.A.S. No.</u> 25068-38-6 <u>% by Wt</u> 100

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Specific Physical Form: Viscous Odor, Color, Grade: transparent, epoxy odor. General Physical Form: Liquid Immediate health, physical, and environmental hazards:

May cause allergic skin reaction.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Vapors released during curing may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

3M MATERIAL SAFETY DATA SHEET SCOTCH-WELD (TM) 2216 B/A Part B Translucent Epoxy Adhesive

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials. Gloves made from the following material(s) are recommended: Polyethylene/Ethylene Vinyl Alcohol.

8.2.3 Respiratory Protection

Avoid breathing of dust created by cutting, sanding, grinding or machining.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with P100 particulate filters, Half facepiece or fullface airpurifying respirator with P95 particulate filters, Half facepiece or fullface air-purifying respirator with N95 particulate filters. Consult the current 3M Respiratory Selection Guide for additional information or call 1-800-243-4630 for 3M technical assistance.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

None Established

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Specific Physical Form:	Viscous
Odor, Color, Grade:	transparent, epoxy odor.
General Physical Form:	Liquid
Autoignition temperature	No Data Available
Flash Point	248 °C [Test Method: Pensky-Mar
Flammable Limits - LEL	Not Applicable
Flammable Limits - UEL	Not Applicable
Boiling point	Not Applicable
Density	1.17 g/ml
Vapor Density	Not Applicable
Vapor Pressure	<=0.03 mmHg [@ 77 °C]
Specific Gravity	1.17 [<i>Ref Std:</i> WATER=1]
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Nil
Evaporation rate	Not Applicable
Volatile Organic Compounds	0 g/l
Percent volatile	0.00 % weight
VOC Less H2O & Exempt Solvents	0 g/l
Viscosity	Approximately 14000 centipoise

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid: Strong acids; Strong oxidizing agents; Heat is generated during cure. Do not cure a mass larger than 50 grams in a confined space to prevent a premature reaction (exothem) with production of intense heat and smoke.

Pensky-Martens Closed Cup]