


Replacement JUMPER WIRES Selection Guide

Part No.	Product I.D.	Length (In.)	Qty/Pkg	Color
923345-01-C	80-6103-3938-6	0.1	200	(No insulation)
923345-02-C	80-6103-3939-4	0.2	200	Red
923345-03-C	80-6103-3940-2	0.3	200	Orange
923345-04-C	80-6103-3941-0	0.4	200	Yellow
923345-05-C	80-6103-3942-8	0.5	200	Green
923345-06-C	80-6103-3943-6	0.6	150	Blue
923345-07-C	80-6103-3944-4	0.7	150	Violet
923345-08-C	80-6103-3945-1	0.8	150	Gray
923345-09-C	80-6103-3946-9	0.9	150	White
923345-10-C	80-6103-3947-7	1.0	100	Brown
923345-20-C	80-6103-3948-5	2.0	100	Red
923345-30-C	80-6103-3949-3	3.0	75	Orange
923345-40-C	80-6103-3950-1	4.0	75	Yellow
923345-50-C	80-6103-3951-9	5.0	75	Green

All Jumper Wires are PVC insulated #22 AWG solid, tinned copper and are recommended for use with all solderless breadboarding units from 3M.



Electronic Specialty Markets
 3M Electronic Products Division
 6801 Riverplace Blvd.
 Austin, Texas 78726-9000

78-8064-7136-9 (200566)