



International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com



GENERAL PURPOSE SQUARE SPEAKER

Part Number: S350SA

MODEL NUMBER	S350SA
FRAME DIAMETER (MM)	92 x 92
FRAME DEPTH (MM)	27
MATERIAL: CONE / FRAME	PAPER / METAL
MAGNET TYPE	ALNICO
MAGNET: SIZE (MM) / WEIGHT (OUNCES/GRAMS)	13 x 10 - 0.36 / 9.92
RATED POWER (WATTS): Nom. / Max.	0.5 / 1.0
VOICE COIL IMPEDANCE (OHMS)	8 ± 15% @ 1000 Hz 1V
RESONANT FREQUENCY (Hz) Without Baffle	190 ± 38
FREQUENCY RESPONSE (Hz)	Fo ~ 12000 ± 10 dB
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	92 ± 3 dB
MEASURED AT:	1W @ 50 CM
MEAN VALUE AT:	500, 600, 800, 1.0K Hz
OPERATION (MUST BE NORMAL)	PROGRAM SOURCE 1 W
BUZZ & RATTLES (MUST BE NORMAL)	SINE WAVE 0.5 W
DISTORTION @ RATED POWER INPUT	5% MAXIMUM @ 1,000 Hz
LOAD TEST (WHITE NOISE)	0.5W @ 5 HOURS
HUMIDITY TEST*	40° ± 2°C 50% R.H. 96 HRS

HEAT TEST*	40° ± 2°C 50% R.H. 96 HRS
OUTSIDE DIAMETER OF YOKE SEAT (MM)	22 - YOKE SIZE: 22 x 14.2 x 12.5
OUTSIDE DIAMETER (ELIMINATE RIM)	86
BAFFLE OPENING (MM)	84
THICKNESS OF RIM (MM)	3.5
NET WEIGHT (OUNCES)	2.04 / 57.8
MOUNTING DIMENSIONS/DIAGONAL (MM)	103 - HOLE SIZE: 5 x 6
POLARITY: DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.	
*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS	

■ DIMENSIONS

■ TYPICAL FREQUENCY RESPONSE CURVE

[Return to top](#)