HBL7467 -- Twist-Lock Flanged Inlet




2P2W, 15A 125V, ML-1P, Stainless Flange, Polarized

Product Specifications

Product Type	Twist-Lock Devices
Product Item	Flanged Inlet
Wiring Scheme	2 Pole, 2 Wire Non-Grounding
Amperage	15A
Voltage	125V AC
NEMA Configuration	ML-1P
Item Style	Standard
Item Version	Polarized
Device Color	Black
Blade Material	Brass
Terminal Screw Material	#5-40 Brass
Flanged Casing Material	.025" Stainless Steel
Mounting Screw Material	Brass, zinc plated
Ratings	Molded into face

Dielectric Voltage Withstand	2,000V minimum.	
Current Interrupting	Certified for current interrupting at full rated current.	
Temperature Rise	Temperature Rise Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.	
Terminal Accommodation	15A #14AWG	
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)	
Flammability	UL 94 VO for Receptacles and Inlets. HB or better for Plugs and Connectors.	
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)	
Catalog Page	Click here for catalog page B2	
Brochures	Click here for product brochure	
Hubbellnet	Click here for Hubbellnet	
Catalog Section	Click here for Section-B	
UPC Number	78358523732	
Weight in LBs	0.1	





TWIST-LOCK® Devices


2 Pole, 2 Wire, Non-Grounding

15 Ampere, 125 Volts

Midget TWIST-LOCK Flanged Receptacle, Plug, Connector Body and Flanged Inlet



HBL7468



HBL7465V



HBL7464V



HBL7466, HBL7467



HBL4890







Flanged Receptacle

Description	Catalog Number
Stainless steel flange, exposed terminals.	HBL7468
-	

Male Plug IP20 SUITABILITY			
Description	Cord Dia.	Catalog Nu	mber
Valise® plug, black nylon.	.220"385" (5.6-9.8)	-	HBL7465V

Connector Body IP20 SUITABILITY			
Description	Cord Dia.	Catalog Number	
Valise connector body, black nylon, polarized.	.220"385" (5.6-9.8)	HBL7464V	-

Flanged Inlets

Description	Catalog Nu	Catalog Numbers	
Stainless steel flange, polarized, exposed terminals.	-	HBL7467	
Stainless steel flange, not polarized, exposed terminals.	-	HBL7466	

Weatherproofing Accessories

Description	Catalog Number	S
Seal-tite® cover, black elastomer, for use with a HBL7465V when used with a HBL7464V connector body or a HBL7464V connector when used with a flanged inlet.	HBL7490V**	*
Seal-tite cover, black elastomer, for use with a HBL7464V connector body and combination of HBL7465V plug and HBL7490V cover.	HBL7459V**	*
Closure cover for use with HBL7466 or HBL7467. Bead chain is nickel-plated.	HBL4890	*

^{**} IP55 suitability when installed and used properly with plug and connector

body combinations.





HBL7490V

^{*} Not UL Listed.