

PANEL MOUNT INDICATOR, NON-RELAMPABLE

NEON AND INCANDESCENT TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

| PART NO. | LENS COLOR | VOLTAGE | CURRENT [mA] | RATED LIFE HOURS |
|--------------------------------|------------|------------|--------------|------------------|
| NEON 115VAC SERIES | | | | |
| WL-1050C1 | RED | 105-125VAC | 1.5mA | 25,000 |
| WL-1050C2 | CLEAR | 105-125VAC | 1.5mA | 25,000 |
| WL-1050C3 | AMBER | 105-125VAC | 1.5mA | 25,000 |
| WL-1050C4 | WHITE | 105-125VAC | 1.5mA | 25,000 |
| WL-1052C5 | GREEN | 105-125VAC | 1.5mA | 25,000 |
| NEON 230VAC SERIES | | | | |
| WL-1051C1 | RED | 208-250VAC | 1.5mA | 25,000 |
| WL-1051C2 | CLEAR | 208-250VAC | 1.5mA | 25,000 |
| WL-1051C3 | AMBER | 208-250VAC | 1.5mA | 25,000 |
| WL-1051C4 | WHITE | 208-250VAC | 1.5mA | 25,000 |
| WL-1053C5 | GREEN | 208-250VAC | 1.5mA | 25,000 |
| INCANDESCENT 12V SERIES | | | | |
| WL-1090C1-12V | RED | 12V-14V | 80mA | 25,000 |
| WL-1090C3-12V | AMBER | 12V-14V | 80mA | 25,000 |
| WL-1090C4-12V | WHITE | 12V-14V | 80mA | 25,000 |
| WL-1090C5-12V | GREEN | 12V-14V | 80mA | 25,000 |
| INCANDESCENT 28V SERIES | | | | |
| WL-1090C1-28V | RED | 24V-28V | 40mA | 25,000 |
| WL-1090C3-28V | AMBER | 24V-28V | 40mA | 25,000 |
| WL-1090C4-28V | WHITE | 24V-28V | 40mA | 25,000 |
| WL-1090C5-28V | GREEN | 24V-28V | 40mA | 25,000 |

NOTES

1. Recommended panel thickness
0.030" to 0.090"
2. 6" leads with 1/2" strip are standard
3. Storage temperature
TSTG: -25°C - +80°C
4. Ambient temperature
TA: -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance
VOP: ± 10%
8. Body Material
Nylon, white
9. Lens Material
Polycarbonate
10. Bezel Material
Stainless steel
11. Wire Gauge
18 AWG
12. Wire Strip
1/2"


CERTIFICATIONS

UL (E340667), RoHS



RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

