HBL7465V -- Twist-Lock Valise Plug




2P2W, 15A 125V, ML-1P, Black Nylon

	1 4 (1	• 6•	4 •
Prod	TICE S	pecifica	none
1100	luct o	pecifica	
		1	

Twist-Lock Devices
Connector Body
2 Pole, 2 Wire Non-Grounding
15A
125V AC
ML-1R
Valise
Black
.218"375" (5.5-9.5)
Black Nylon
Black nylon
Nylon
Brass
Cold rolled steel-nickel-plated
#8-32 Steel (copper flash, nickel plate & molykote)

Cord Clamp Screw Material	Steel-zinc-plated
Body Holding Screw Material	Steel-zinc-plated
Ratings	Molded into face
Dielectric Voltage Withstand	2000V minimum
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.
Terminal Accommodation	15A-#14AWG
Terminal Identification	Terminals identified in accordance with UL 498 (Black, White)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Moisture Resistance	IP20
Catalog Page	Click here for catalog page B2
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358523728
Weight in LBs	0.1





TWIST-LOCK® Devices

2 Pole, 2 Wire, Non-Grounding

15 Ampere, 125 Volts

Midget TWIST-LOCK Flanged Receptacle, Plug, Connector Body and Flanged Inlet



HBL7468



HBL7465V



HBL7464V



HBL7466, HBL7467



HBL4890







Flanged Receptacle

Description	Catalog Number	
Stainless steel flange, exposed terminals.	HBL7468	
-		

Male Plug IP20 SUITABILITY			
Description	Cord Dia.	Catalog Nu	mber
Valise® plug, black nylon.	.220"385" (5.6-9.8)	-	HBL7465V

Connector Body IP20 SUITABILITY			
Description	Cord Dia.	Catalog Number	
Valise connector body, black nylon, polarized.	.220"385" (5.6-9.8)	HBL7464V	-

Flanged Inlets

Description	Catalog Numbers	
Stainless steel flange, polarized, exposed terminals.	-	HBL7467
Stainless steel flange, not polarized, exposed terminals.	-	HBL7466

Weatherproofing Accessories

Description	Catalog Number	S
Seal-tite® cover, black elastomer, for use with a HBL7465V when used with a HBL7464V connector body or a HBL7464V connector when used with a flanged inlet.	HBL7490V**	*
Seal-tite cover, black elastomer, for use with a HBL7464V connector body and combination of HBL7465V plug and HBL7490V cover.	HBL7459V**	*
Closure cover for use with HBL7466 or HBL7467. Bead chain is nickel-plated.	HBL4890	*

^{**} IP55 suitability when installed and used properly with plug and connector

body combinations.





HBL7490V

^{*} Not UL Listed.