HBL2721 -- Twist-Lock Plug



2.33 3P4W, 30A 3PH 250V, L15-30P, Black & White Nylon

HBL2711

Product Specifications

Product Type Twist-Lock Devices **Product Item** Plug Wiring Scheme 3 Pole, 4 Wire Grounding Amperage 30A 3 Phase 250V AC Voltage **NEMA Configuration** L15-30P **Item Style** Insulgrip **Device Color** Black/White Horsepower Cord Dia. .35"-1.15" (9-29) Natural White Nylon **Blade Holder Material Terminal Retainer Material** Clear polycarbonate **Housing Material** Black nylon **Cord Clamp Material** Natural (white) nylon

Blade Material	Brass	
Terminal Clamp Material	.08" (2) steel-nickel plated	
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive	
Ground Screw Material	#10-32 Brass (green finish) Multi-drive	
Cord Clamp Screw Material	Steel, zinc plated Multi-drive	
Body Holding Screw Material	Steel, zinc plated Multi-drive	
Ratings	Molded into face	
Catalog No.	Permanently ink marked on body.	
Dielectric Voltage Withstand	2,000V minimum	
Current Interrupting	Certified for current interrupting at full rated current.	
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.	
Cord Accommodation	Round portable service cords of diameters commensurate with the device rating as defined in UL Standard 62, CSA C22.2 No. 49.	
Terminal Accommodation	30A #10 AWG	
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)	
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6	
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)	
Moisture Resistance	IP20	
Listings	FED SPEC UL/CSA	
Catalog Page	Click here for catalog page B40	
Brochures	Click here for product brochure	
Hubbellnet	Click here for Hubbellnet	
Catalog Section	Click here for Section-B	
UPC Number	78358503922	
Weight in LBs	0.25	
-		



NEMA Configuration





TWIST-LOCK® Devices

3 Pole, 4 Wire Grounding

30 Ampere, 125/250 Volts and 3Ø 250 Volts

Receptacles, INSULGRIP® Connector Bodies, Flanged Devices and Plugs









Single Flush Receptacles, **Back and Side Wired** UL/CSA 2 (2) HP UL/CS. 3 HP Description **Catalog Numbers** Black nylon face. HBL2710 HBL2720 IG2710 IG2720 Isolated ground, orange nylon face.



Insulgrip Connector Bodies IP20 SUITABILITY

Description	Catalog Numbers	
Black and white nylon.	HBL2713	HBL2723
Corrosion resistant, yellow nylon.	HBL27CM13	HBL27CM23
N. (O I I O O O O O O O O O O O O O O O O		

Note: Cord clamp range .35"-1.15" (9-29).

3.06" (77.7) 120°
1.34" R (34.0)
.19" (4.8) 120° DIA.
(57.7)
2.23" (56.6)

Insulgrip Flanged Receptacles

Description	Catalog Numb	ers
Nylon casing, back wired.	HBL2716	HBL2726







	_	 -
2.21" (56.1)		2.33" (59.2)

Insulgrip Plugs IP20 SUITABILITY

Description	Catalog Number	ers
Black and white nylon.	HBL2711	HBL2721
Corrosion resistant, yellow nylon.	HBL27CM11	HBL27CM21

Notes: Cord clamp range .35 "-1.15" (9-29). See page B-73 for Add-A-Shroud™ kit.

HBL2711

3.06" (77.7) 1.34" R (34.0) .19" 120 (4.8) DIA. 2.27" (57.7) 2.23"_(56.6) HBL2715

Insulgrip Flanged Inlets

Description	Catalog Num	Catalog Numbers	
Nylon casing, back wired.	HBL2715	HBL2725	

Notes: HP ratings not in parentheses are phase to phase. HP rating in parentheses is phase to neutral. Only receptacles and plugs are HP rated. See pages B-70 and B-71 for accessories. For technical information see page B-83. See page B-63 for switched enclosure.