

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.500"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
<b>NEON 115VAC SERIES</b>				
WL-1050QC1	RED	105-125VAC	1.5mA	25,000
WL-1050QC2	CLEAR	105-125VAC	1.5mA	25,000
WL-1050QC3	AMBER	105-125VAC	1.5mA	25,000
WL-1050QC4	WHITE	105-125VAC	1.5mA	25,000
WL-1052QC5	GREEN	105-125VAC	1.5mA	25,000
<b>NEON 230VAC SERIES</b>				
WL-1051QC1	RED	208-250VAC	1.5mA	25,000
WL-1051QC2	CLEAR	208-250VAC	1.5mA	25,000
WL-1051QC3	AMBER	208-250VAC	1.5mA	25,000
WL-1051QC4	WHITE	208-250VAC	1.5mA	25,000
WL-1053QC5	GREEN	208-250VAC	1.5mA	25,000
<b>INCANDESCENT 12V SERIES</b>				
WL-1090QC1-12V	RED	12V-14V	80mA	25,000
WL-1090QC3-12V	AMBER	12V-14V	80mA	25,000
WL-1090QC4-12V	WHITE	12V-14V	80mA	25,000
WL-1090QC5-12V	GREEN	12V-14V	80mA	25,000
<b>INCANDESCENT 28V SERIES</b>				
WL-1090QC1-28V	RED	24V-28V	40mA	25,000
WL-1090QC3-28V	AMBER	24V-28V	40mA	25,000
WL-1090QC4-28V	WHITE	24V-28V	40mA	25,000
WL-1090QC5-28V	GREEN	24V-28V	40mA	25,000

## NOTES


1. Recommended panel thickness  
0.030" to 0.090"
2. .187" terminals are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +80°C
4. Ambient temperature  
 $T_A$ : -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance  
 $V_{OP}$ : ±10%
8. Body material  
Nylon, white
9. Lens material  
Polycarbonate
10. Bezel material  
Stainless steel
11. .250" terminals available upon request

## CERTIFICATIONS

UL (E340667), RoHS



## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

