
HBL5261 -- Heavy Duty Specification Grade Single Receptacle



2P3W, 15A 125V, 5-15R, Flush Nylon Face, Back and Side Wired, Brown

Product Specifications

Product Type




Flush Receptacles

Receptacle Style	Single
Face Shape	Standard
Standard	NEMA
Amperage	15A
Voltage	125V
Poles and Wires	2 Pole, 3 Wire Grounding
Wiring Method	Back and Side
Hospital Grade ?	No
Receptacle Grade	Heavy Duty Spec Grade
Face Style	Finder Groove

Color	Brown	
Other Available Colors	Brown, Ivory	
NEMA No.	5-15R	
Horsepower	0.5	
Description	Heavy Duty Straight Blade Single Receptacle	
Type	2 Pole, 3 Wire, Grounding	
Rating	15A, 125V	
Certification	UL Listed to UL 498 File E2186, Guide RTRT Fed Spec WC596G, Meets WD-6 requirements, Certified to CSA, C22.2, No. 42 File 285.	
Terminal Screw Material	#8-32 Brass /Ni plated for neutral	
Ground Screw Material	#8-32 Brass, Multiple Drive (Green)	
Wire Clamps Material	.062" (1.6) Steel - Ni. Plated	
Top Material	Nylon	
Base Material	Reinforced PET	
Power Contacts Material	.032" (.81) Brass	
Mounting Strap Material	.050" (1.3) Brass	
Auto Ground Clip Material	Stainless Steel	
Mounting Screw Material	Steel-Zinc Plated	
Dielectric Voltage	Withstands 2,000V minimum.	
Current Interrupting	Certified for current interrupting at full rated current.	
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%	
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).	
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only.	
Product Identification	Ratings are a permanent part of the device.	
Flammability	UL 94 V2 or better	
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).	
M Drawings	Click here for M-Drawing	
Catalog Page	Click here for catalog page A5	

Brochures	Click here for product brochure
Catalog Section	Click here for Section-A
UPC Number	78358501385
Weight in LBs	0.15





Straight Blade Devices

2 Pole, 3 Wire Grounding

15 and 20 Ampere, 125 Volts

Heavy Duty, Specification Grade and Hospital Grade **Duplex and Single Receptacles**











Heavy Duty, Specification Grade, **Duplex Receptacles**

Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired, multiple drive screws.	Brown Ivory Gray Red White Black	HBL5262 HBL5262I HBL5262GY HBL5262R HBL5262W HBL5262BK	HBL5362 HBL5362I HBL5362GY HBL5362R HBL5362W HBL5362BK
Corrosion resistant.	Yellow Ivory	HBL52CM62 HBL52CM62I	HBL53CM62
On 4" (101.6) round cover.	Brown	HBL5282	_
Isolated ground. ⁽¹⁾	Orange Ivory Gray White Red	IG5262 IG5262I IG5262GY - IG5262R	IG5362 IG5362I IG5362GY IG5362W IG5362R

Heavy Duty, Hospital Grade, **Duplex Receptacles**

Description	Color	Catalog Numbers	
Flush, thermoplastic polyester face, back and side wired, multiple drive screws.	Brown	HBL8200	HBL8300
	Ivory	HBL8200I	HBL8300I
	Gray	HBL8200GY	HBL8300GY
	Red	HBL8200R	HBL8300R
	White	HBL8200W	HBL8300W

Heavy Duty, Specification Grade, Single Receptacles

Description	Color	Catalog Num	bers
Flush, nylon face, back and side wired, multiple drive screws.	Brown	HBL5261	HBL5361
	Ivory	HBL5261I	HBL5361I
	Gray	-	HBL5361GRY


Special Purpose Single Receptacles


Description	Color	Catalog Numbers	
Corrosion resistant.	Yellow	HBL52CM61	HBL53CM61
Isolated ground.(1)	Orange	IG5261	IG5361
Panel mount on 1.94" (49.3) centers.	Brown	HBL5284	HBL5357

Heavy Duty, Hospital Grade, Single Receptacles


Description	Color	Catalog Numbers	
Flush, nylon face, back and side wired, multiple drive screws. ⁽²⁾	Brown	HBL8210	HBL8310
	Ivory	HBL8210I	HBL8310I
	Gray	HBL8210GY	HBL8310GY
	Red	HBL8210R	HBL8310R
	White	HBL8210W	HBL8310W
Isolated ground.(1)	Orange	IG8210	IG8310
Panel mount on 1.94" (49.3) centers.	Brown	HBL8284	_
	Ivory	HBL8284I	HBL8384I

Notes: (1) See Section J for full line of isolated ground devices. (2) See Section I for full line of hospital grade devices.






HBL5362I



HBL8200GY



1.39" 1.94" (35.3) (49.3)

HBL5284