HBL560R9W -- Watertight IEC Pin and Sleeve Receptacle



Every Hubbell non-metallic Pin and Sleeve product is designed to meet the International Standard IEC 60309-1 and IEC 60309-2. This device standard calls out singly rated, non-interchangeable configuration for every voltage and type of service throuought the world.


Product Specifications		
Product Type	IEC Devices	
Device Standard	IEC	
IEC Product Type	Watertight	
Service Style	Standard	
Device	Receptacle	
Amperage	60A	
Voltage	3 Phase Y 120/208V	
Poles and Wires	4 Pole, 5 Wire	
Color	Blue	


Replacement Interior Number	IN560EF	
Hinge Spring	Stainless Steel (300 series)	
Housing	Zytel 101 Nylon	
Mounting Flange	Zytel 101 Nylon	
Mounting Screws	Stainless Steel (300 Series)	
Contact Carrier	High-Impact Thermoset	
Retainer	High-Impact Thermoset	
Terminal Screws	Stainless Steel (300 series)	
Assembly Screws	Stainless Steel (300 series)	
Gaskets	Neoprene	
Cover Arm	Rynite SST35	
Arm Spring	Stainless Steel (17-1 Type)	
Cover	Rynite SST35	
Cover Screw/Rivet	Nickel Plated Brass	
Rotating Sealing Disc	Polycarbonate	
Ground/Phase Sleeve	Brass	
Pin/Sleeve Spring	Beryllium Copper multi-contact insert with silver plating.	
Certification	UL Listed, CSA Certified	
Dielectric Withstand Voltage	Withstands 3,000V AC	
Max Working Voltage	600V AC RMS	
Current Interrupting	Certified for current interrupting at full rated current.	
Short Circuit Withstand	Suitable for use on a circuit capable of delivering not more than 10,000 RMS symmetrical amperes at the voltage rating of the receptacle.	
Temperature Rise	Max 30° C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%.	
Endurance	Mechanical: 10,000 cycles, Electrical: 6,000 cycles.	
Impact Resistance	In accordance with UL746C	
Terminal Identification	Terminals identified in accordance with North American and International conventions.	
Product Identification	Identification and ratings are a part of the external label and molded into the receptacle mount.	
Moisture Resistance	Watertight per IEC 60309-1	
Ingress Protection	IP67 Suitability	
Flammability	UL94-5VA and V-0 classification.	
Operating Temperatures	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact.	
UV Resistance	All materials are UV Stabilized.	

Industry	Watertight
Agriculture	Outdoor for fans, heaters, pumps, etc.
Chemical Processing	Where subject to water, corrosion and rough use.
Certifications	UL Listed, CSA Certified.
Catalog Page	E-5
M Drawings	Click here for M-Drawing
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-E
UPC Number	78358540573
Weight in LBs	2.55



Watertight Application Guide





Hubbell Incorporated (Delaware) 185 Plains Road Milford, CT 06460-2420

Ph: (203) 882-4800 Fax: (800) 255-1031

