



Product Datasheet		Catalog Home Home Page Search	
<h2>PC100 -- Pin and Sleeve Products</h2>			
		<p>Closure Cap, 100A Pin and Sleeve Males</p>	
PC3430			
Product Specifications			
Product Type	 <p>Replacement Items</p>		
Replacement Part	Plug Cover		
For Use With	IEC Devices		
Hinge Spring	Stainless Steel (300 series)		
Assembly Screws	Stainless Steel (300 series)		
Gaskets	Neoprene		
Certification	UL Listed, CSA Certified		
Dielectric Withstand Voltage	Withstands 3,000V AC		
Max Working Voltage	600V AC RMS		
Current Interrupting	Certified for current interrupting at full rated current.		
Short Circuit Withstand	Suitable for use on a circuit capable of delivering not more than 10,000 RMS symmetrical amperes at the voltage rating of the receptacle.		
Endurance	Mechanical: 10,000 cycles, Electrical: 6,000 cycles.		
Impact Resistance	In accordance with UL746C		
Terminal Identification	Terminals identified in accordance with North American and International conventions.		
Product Identification	Identification and ratings are a part of the external label and molded into the receptacle mount.		
Ingress Protection	IP67 Suitability		
Flammability	UL94-5VA and V-0 classification.		
Operating Temperatures	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact.		
UV Resistance	All materials are UV Stabilized.		
Certifications	UL Listed, CSA Certified.		
Device Description	Cap assemblies provide watertight sealing to a disconnected male Pin and Sleeve plug or inlet. Manufactured out of the same tough nonmetallic material as the watertight Pin and Sleeve devices for corrosion and abuse resistance.		
UPC Number	78358537100		
Weight in LBs	0.45		
Link to Drawing Library	Click here for Library		
Link to PDF Catalog	Click here for Catalog		

