

T3¼ MINIATURE BAYONET BASE LED LAMP

AC OPERATION

130VAC, 230VAC

PART NO.	COLOR	VOLTAGE V _{OP} [VAC]	CURRENT I _{OP typ.} [mA]	LUMI. INTENSITY LED I _{V typ.} [mcd]	DOMINANT WAVELENGTH λ _D [nm]
130VAC SERIES ^[6]					
WL-18606130	RED	130VAC	5	800	630
WL-18606131	GREEN	130VAC	5	800	525
WL-18606132	YELLOW	130VAC	5	200	589
WL-18606137	BLUE	130VAC	5	250	470
WL-1860613W3	WHITE CLEAR	130VAC	5	530	*
WL-1860613W3D	WHITE DIFFUSED	130VAC	5	280	*
230VAC SERIES ^[7]					
WL-18606230	RED	230VAC	3	500	630
WL-18606231	GREEN	230VAC	3	470	525
WL-18606232	YELLOW	230VAC	3	150	589
WL-18606237	BLUE	230VAC	3	220	470
WL-1860623W3	WHITE CLEAR	230VAC	3	320	*
WL-1860623W3D	WHITE DIFFUSED	230VAC	3	180	*

*Chromaticity coordinates X=0.31 Y=.032


NOTES

1. Storage temperature
T_{STG}: -25°C – +80°C
2. Ambient temperature
T_A: -20°C – +60°C
3. AC operation only
4. Voltage tolerance
V_{OP}: ±10%
5. Electro-optical ratings at
T_A=25°C
6. This LED lamp was developed to operate on a supply voltage of 130VAC only. Operating at a higher supply voltage using commercial lamp holders with integrated resistors is not approved
7. This LED lamp was developed to operate on a supply voltage of 230VAC. This version may be used in a lamp holder with integrated resistors to replace 130V 20mA incandescent lamps
8. Due to production tolerances, slight color variations may be detected within individual consignments
9. Base Type: BA9s

CERTIFICATIONS

RoHS
COMPLIANT

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm

OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

