

# T3¼ MINIATURE BAYONET BASE TRIO-LED LAMP

## AC/DC OPERATION

### WITH HALF WAVE RECTIFIER

PART NO.	COLOR	VOLTAGE	CURRENT	LUMI. INTENSITY	DOMINANT
		V <sub>OP</sub> [V] AC/DC	I <sub>OP typ.</sub> [mA] AC/DC	LED **I <sub>v typ.</sub> [mcd]	WAVELENGTH λ <sub>D</sub> [nm]
WL-18620350	RED	24V	9/17	3 x 2800	630
WL-18620351	GREEN	24V	9/17	3 x 2600	525
WL-18620352	YELLOW	24V	9/17	3 x 700	589
WL-18620357	BLUE	24V	9/17	3 x 800	470
WL-1862035W3	WHITE CLEAR	24V	9/17	3 x 1900	*
WL-1862035W3D	WHITE DIFFUSED	24V	9/17	3 x 900	*
WL-18620450	RED	28V	9/17	3 x 2800	630
WL-18620451	GREEN	28V	9/17	3 x 2600	525
WL-18620452	YELLOW	28V	9/17	3 x 700	589
WL-18620457	BLUE	28V	9/17	3 x 800	470
WL-1862045W3	WHITE CLEAR	28V	9/17	3 x 1900	*
WL-1862045W3D	WHITE DIFFUSED	28V	9/17	3 x 900	*

\*Chromaticity coordinates X=0.31 Y=.032

\*\*Luminous intensity data of the used LEDs at: I<sub>OP</sub> DC


## NOTES

1. Storage temperature  
T<sub>STG</sub>: -25°C – +80°C
2. Ambient temperature  
T<sub>A</sub>: -20°C – +60°C
3. AC/DC operation
4. Voltage tolerance  
V<sub>OP</sub>: ±10%
5. Electro-optical ratings at  
T<sub>A</sub>=25°C
6. These Wamco LED lamps include a protection diode and can be used on DC and AC voltage. The typical light reduction on AC voltage is approx. 25%
7. Due to production tolerances, slight color variations may be detected within individual consignments
8. Base Type: BA9s

## CERTIFICATIONS

**RoHS**  
COMPLIANT

## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

