

SLI Series units act as a defensive barrier between your equipment and

against five power problems.



Power Surges

Under voltage



Over voltage

SLI Series Features

- 230 VAC, 50/60 Hz (Auto-sensing) Operation
- Advanced Battery Management Technology Doubles Battery Service Life
- Extended Battery Modules (EBMs) Increase Run Time Capacity
- Buck and Double Boost Voltage Regulation
- Load Segment Control
- Network Transient Protector Isolates Networks, Modems and Cables from Surges and Spikes
- Hot-swappable Batteries Simplify Service
- X-Slot Option Cards Extend Power Management Capabilities

Advanced Power Management

corrupted power, thereby eliminating premature hardware

failure, data loss and error, storage loss and system/keyboard

SLI Series STABILINE Uninterruptible Power Supplies provide advanced power management for PC's, workstations and servers.

lockup. SLI Series units are most effective

All SLI Series units incorporate load segment capabilities (separate receptacle groups) which enable scheduled shutdowns and load shedding as well as maximum run time for each critical device. To preserve battery power for more critical equipment connected to the UPS, shut down and power up load segments are user-defined. Feature rich communications and UPS power management software provide extensive control and monitoring.

All feature advanced battery management technology, which doubles battery service life, critical to maximizing system availability. Lead-acid batteries subjected to constant trickle charging (utilized by most all other UPSs on the market today) reach the end of their useful life in less than half the time of batteries charged using SLI Series advanced battery management. Utilizing a proprietary three-stage charging technique, SLI Series units minimize recharge time and provide for up to 60 days notification when batteries are approaching the end of their useful life.

Hot-swappable Batteries

When alarm notification indicates the end of battery life is near, batteries can easily be hot-swapped without powering down the connected load(s). User friendly design allows batteries to be exchanged through the front of the unit.

Extended Battery Modules

Increasing battery backup time is as simple as plugging in an extended battery module. Hot-swap capability with all extended battery modules (EBMs) allow for expanded run time or EBM replacement while keeping your critical load up and running.

		Model	Model	Model	
-		SLI1000X SLI1500X SLI2200X			
INPUT	Nominal Voltage	230 VAC			
Q	Voltage Range Frequency Range	154 - 288 VAC			
Z	Noise Filtering	46 - 65 Hz MOVs and Line Filter for Normal and Common-mode Noise			
_	· ·				
	VA Rating	1000 VA	1500 VA	2200 VA	
	Power	700 Watts	1050 Watts	1600 Watts	
—	Frequency		50/60 Hz, Auto-sensing 230 VAC		
$\dot{\Box}$	Voltage Voltage Regulation	ZSU VAC			
<u>_</u>	On Utility	-10% to +6% of Nominal			
OUTPUT	On Battery		±5% RMS		
	Overload (Normal Operation)	110% Overload, Shutdown After 3 Minutes; 150% Overload, Shutdown 10 Cycles			
	Voltage Wave Shape (Battery Mode)	Sine Wave			
	Transfer Time Line Fails/Recovers		2-4 ms Typical		
	Output Protection	Short Circuit Protection			
	DC Voltage	24 VDC	48 VDC	48 VDC	
	Type		d, Lead-acid, Maintenance-free, Valve-regulat		
	Number (Internal)	(2) 12V, 9AH	(4) 12V, 7AH	(4) 12V, 12AH	
111	Number (External Battery Module)	(8) 12V, 9AH	(8) 12V, 9AH	(8) 12V, 9AH	
出	Recharge Time to 90%	Internal Battery; <	3 Hours; External Battery; No More than 1	6 x Discharge Time	
	Run Time (Internal Batteries) †				
BATTERY	Full Load/Half Load in Minutes	5/14	6/17	5/14	
	Battery Replacement		Internal Batteries and External Battery Modu		
	Monitoring	Advanced Monitoring for Earlier Failure Detection and Warning; Auto Detection of Additional EBMs			
S	Special Diagnostics	Frequency Auto Tracking, DC Cold Start, Optional Extended Battery Modules, Load Segment Control, Network Transient Protection; Input/Output RJ45 (accomodates RJ11 Jacks) for Modem/Fax and Other Telecommunications Equipment; UL 497A Tested Full System Self-test on Power-up			
	User Interface	Front Panel Control			
	Computer Interface	Power Management Software CD-ROM and 6-Foot Communications Cable Supplied			
	X-Slot Interface	RS-232 Single Serial Card (Standard); Other Options Available - Consult Factory			
\cong	Audible	On Battery, Low Battery, Overload, UPS Fault			
RAL SPECIFICATIONS	Temperature <u>Operating</u>	0°C to 40°C (32°F to 104°F)			
	Storage	0°C to 25°C (32°F to 77°F)			
	Transit	-25°C to 55°C (-13°F to 131°F)			
	Humidity Altitude Operating	0-95% Non-condensing 10,000 Feet (3,000 Meters) Without Derating			
	Transit	50,000 Feet (15,000 Meters Above Sea Level)			
	Audible Noise	Less than 40 dBA Normal Mode, Less than 55 dBA Battery Mode with Typical Load			
10	Surge Suppression	ANSI/IEEE C62.41 Category B (Formerly IEEE 587), IEC61000-4-5			
0)	EMC Compliance	FCC Part 15, ICES-003			
	Input Connection	10A, IEC-320 Inlet, (2) IEC Interconnect Cables Supplied			
N N	Output Receptacles	(6) 10A, IEC-320 (C13)	(6) 10A, IEC-320 (C13)	(9) 10A, IEC-320 (C13)	
GENER	Load Segments	(2) Receptacle Groups	(2) Receptacle Groups	(3) Receptacle Groups	
	Weight UPS EBM	34 lbs (16 kg)	51 lbs (23 kg) 60 lbs (27 kg)	68 lbs (31 kg)	
	Dimensions HxWxD UPS Inches	9.45 x 6.38 x 15.79	9.84 x 6.38 x 18.39	9.84 x 8.07 x 19.41	
5	Millimeters	240 x 162 x 401	250 x 162 x 467	250 x 205 x 493	
	EBM Inches		9.84 x 6.38 x 18.66		
	Millimeters		250 x 162 x 474		
	Agency	UL, CUL, CE			
	Warranty		2 Years		
OPTIONAL EBM's		Model	Model	Model	
	Run Time Internal battery plus	SLI24V-EBM	SLI48V-EBM	SLI48V-EBM	
	number of optional EBM's up to four.	Full Load/Half Load in Minutes	Full Load/Half Load in Minutes	Full Load/Half Load in Minutes	
	1 EBM	25/60	33/79	25/60	
	2 EBM TO TO	55/170	63/146	55/170	
	3 EBM	83/199	92/174	81/198	
	4 EBM	109/228	120/201	106/224	

Specifications subject to change without notice. † Backup times are for reference only. Actual duration may vary depending on temperature, battery condition and type of load.



