


# GG-10 AIRCRAFT WARNING LAMP

## SINGLE CONTACT INDEX BAYONET BASE

26.5V 26W

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE	
WL-628	GG-10	BAY15s	26.5V 26W	CC-6	
TEST VOLTS	CURRENT (A)			LIGHT DISTRIBUTION	LIFE HRS
	MIN	NOM	MAX		
26.5V	.910	.980	1.05	SEE TABLE BELOW	300

### DIMENSIONAL CHARACTERISTICS



#### LIGHT DISTRIBUTION CONTAINING FLIGHT AXIS (0°)

##### HORIZONTAL PLANE, PASSING THROUGH LIGHT CENTER AND CENTER OF INDEXING PINS

200 CANDLE POWER MINIMUM	2° INBOARD TO 15° OUTBOARD
25 CANDLE POWER MINIMUM	15° OUTBOARD TO 100° OUTBOARD

##### VERTICAL PLANE, PASSING THROUGH LIGHT CENTER AND PERPENDICULAR TO HORIZONTAL PLANE ABOVE

180 CANDLE POWER MINIMUM	0° TO 20° ABOVE AND BELOW FLIGHT AXIS
20 CANDLE POWER MINIMUM	20° TO 80° ABOVE AND BELOW FLIGHT AXIS

### NOTES

1. Finish clear, except where reflective surface is required
2. Reflective coating must conform to the coating adhesion requirements of MIL-L-6363F, paragraph 4.6.6
3. Part mark WL-628, 26.5V, 26W
4. RoHS compliant
5. ANSI trade number 628

