


# T-4 DOUBLE CONTACT BAYONET BASE

## HALOGEN LAMP

28V 150W

WAMCO PART NO.		ENVELOPE SIZE			BASE TYPE		RATING		FILAMENT SHAPE	
WL-1987		T-4			BA15d		28V 150W		CC-6	
TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			COLOR TEMP	LIFE HRS		
	MIN	NOM	MAX	MIN	NOM	MAX				
28V	4.82	5.36	5.90	204	240	276	3,000°K	700		

## DIMENSIONAL CHARACTERISTICS



## NOTES

1. Lamp clean with no foreign materials or glass chips inside
2. Envelope clear and free of scratches, discoloration, and any cement residue
3. Nickel-plated base
4. Part mark WL-1987
5. RoHS compliant
6. ANSI trade number 1987

