

# SKINTOP® DIX BUSHINGS



Multiple Cable Sealing Bushing for PG & NPT SKINTOP® Cable Glands

SKINTOP® DIX is a multiple hole sealing bushing designed to allow several cables to be inserted through one cable gland. This results in a reduction of space and cost, as a separate cable gland is not required for each cable.




## Technical Data:

Color:	Natural
Materials:	Silicone
Temperature:	-30°C to +100°C
Seal:	IP 54 IP 68 when all holes are optimally filled.

Part Number	Thread Type & Size	Thread Type & Size	# of Holes	Size of Holes		Standard Pack Size
				inches	mm	
53607225	PG-7	-	2	.098	2.5	100
53607417	PG-7	-	4	.067	1.7	100
53609230	PG-9	NPT-3/8"	2	.118	3.0	100
53611225	PG-11	-	2	.098	2.5	100
53611240	PG-11	-	2	.157	4.0	100
53611330	PG-11	-	3	.118	3.0	100
53611430	PG-11	-	4	.118	3.0	100
53613250	PG-13	NPT-1/2"	2	.197	5.0	100
53613340	PG-13	NPT-1/2"	3	.157	4.0	100
53613440	PG-13	NPT-1/2"	4	.157	4.0	100
53616140	PG-16	-	1	.157	4.0	50
53616225	PG-16	-	2	.098	2.5	50
53616240	PG-16	-	2	.157	4.0	50
53616260	PG-16	-	2	.236	6.0	50
53616340	PG-16	-	3	.157	4.0	50
53616350	PG-16	-	3	.197	5.0	50
53616356	PG-16	-	3	.220	5.6	50
53616360	PG-16	-	3	.236	6.0	50
53616440	PG-16	-	4	.157	4.0	50
53616450	PG-16	-	4	.197	5.0	50
53616540	PG-16	NPT-3/4"	5	.157	4.0	50
53621270	PG-21	NPT-3/4"	2	.276	7.0	50
53621280	PG-21	NPT-3/4"	2	.315	8.0	50
53621370	PG-21	NPT-3/4"	3	.276	7.0	50
53621380	PG-21	NPT-3/4"	3	.315	8.0	50
53621460	PG-21	NPT-3/4"	4	.236	6.0	50
53621550	PG-21	NPT-3/4"	5	.197	5.0	50
53621640	PG-21	NPT-1"	6	.157	4.0	50
53629290	PG-29	NPT-1"	2	.354	9.0	50
53629390	PG-29	NPT-1"	3	.354	9.0	50
53629470	PG-29	NPT-1"	4	.276	7.0	50
53629480	PG-29	NPT-1"	4	.315	8.0	50
53629490	PG-29	NPT-1"	4	.354	9.0	50
53629556	PG-29	NPT-1"	5	.220	5.6	50
53629570	PG-29	NPT-1"	5	.276	7.0	50
53629675	PG-29	-	6	.295	7.5	50

# SKINTOP® DIX-DV INSERTS

Inserts for SKINTOP® DIX NPT, PG & Metric



SKINTOP® DIX-DV inserts are designed to seal unused positions in SKINTOP® DIX bushings, which need to be closed to ensure the proper class protection.

## Technical Data:

Materials:	Polyamide
------------	-----------

Part Number	Diameter		Length		Standard Pack Size
	inches	mm	inches	mm	
53100003	.118	3.0	.354	9	100
53100004	.157	4.0	.354	9	100
53100005	.197	5.0	.433	11	100
53100006	.236	6.0	.551	14	100
53100007	.276	7.0	.551	14	100
53100008	.315	8.0	.551	14	100
53100009	.354	9.0	.551	14	100