


GG-10 AIRCRAFT WARNING LAMP

SINGLE CONTACT INDEX BAYONET BASE

14V 26W

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE	
WL-A-7512-12	GG-10	BAY15s	14V 26W	C-6	
TEST VOLTS	CURRENT (A)			LIGHT DISTRIBUTION	LIFE HRS
	MIN	NOM	MAX		
14V	1.72	1.86	2.00	SEE TABLE BELOW	300

DIMENSIONAL CHARACTERISTICS



LIGHT DISTRIBUTION CONTAINING FLIGHT AXIS (0°)

HORIZONTAL PLANE, PASSING THROUGH LIGHT CENTER AND CENTER OF INDEXING PINS	
200 CANDLE POWER MINIMUM	2° INBOARD TO 15° OUTBOARD
25 CANDLE POWER MINIMUM	15° OUTBOARD TO 100° OUTBOARD
VERTICAL PLANE, PASSING THROUGH LIGHT CENTER AND PERPENDICULAR TO HORIZONTAL PLANE ABOVE	
180 CANDLE POWER MINIMUM	0° TO 20° ABOVE AND BELOW FLIGHT AXIS
20 CANDLE POWER MINIMUM	20° TO 80° ABOVE AND BELOW FLIGHT AXIS

NOTES

1. Finish clear, except where reflective surface is required
2. Reflective coating must conform to the coating adhesion requirements of MIL-L-6363F, paragraph 4.6.6
3. Part mark WL-A-7512-12, 14V, 26W
4. RoHS compliant
5. ANSI trade number 7512-12, ARP881 7512-12

