


# GG-10 AIRCRAFT WARNING LAMP

## SINGLE CONTACT INDEX BAYONET BASE

28V 26W

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE	
WL-A-7512-24	GG-10	BAY15s	28V 26W	CC-6	
	CURRENT (A)				
TEST VOLTS	MIN	NOM	MAX	LIGHT DISTRIBUTION	LIFE HRS
28V	.860	.930	1.00	SEE TABLE BELOW	300

## DIMENSIONAL CHARACTERISTICS



### LIGHT DISTRIBUTION CONTAINING FLIGHT AXIS (0°)

HORIZONTAL PLANE, PASSING THROUGH LIGHT CENTER AND CENTER OF INDEXING PINS	
200 CANDLE POWER MINIMUM	2° INBOARD TO 15° OUTBOARD
25 CANDLE POWER MINIMUM	15° OUTBOARD TO 100° OUTBOARD
VERTICAL PLANE, PASSING THROUGH LIGHT CENTER AND PERPENDICULAR TO HORIZONTAL PLANE ABOVE	
180 CANDLE POWER MINIMUM	0° TO 20° ABOVE AND BELOW FLIGHT AXIS
20 CANDLE POWER MINIMUM	20° TO 80° ABOVE AND BELOW FLIGHT AXIS

## NOTES

1. Finish clear, except where reflective surface is required
2. Reflective coating must conform to the coating adhesion requirements of MIL-L-6363F, paragraph 4.6.6
3. Part mark WL-A-7512-24, 28V, 26W and M6363/2-2
4. RoHS compliant
5. ANSI trade number 7512
6. Military standards M6363/2-2, MS25309-7512
7. QPL certified

