



Search

HomeProductsSupportServicesSelectorsHow to Buy

APC Smart-UPS XL 24V Battery Pack

Includes: User Manual

Email Technical Specifications

Printer Friendly

Additional Information

Product Distribution





[+] More Images

Technical Specifications

□ Batteries & Runtime

Battery Volt-Amp-Hour Capacity	816
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte: leakproof
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

□ Physical

Net Weight	69.00 lbs. (31.36 kg)
Maximum Height	8.50 inches (216 mm)
Maximum Width	6.70 inches (170 mm)
Maximum depth	17.30 inches (439 mm)
Shipping Weight	73.00 lbs. (33.18 kg)
Shipping Width	12.60 inches (320 mm)
Shipping Height	15.25 inches (387 mm)
Shipping Depth	23.25 inches (591 mm)
Color	Black
Units per Pallet	24.00

Environmental

Operating Environment $0 - 40 \,^{\circ}\text{C} \, (32 - 104 \,^{\circ}\text{F})$

Options:

- O Replacement Battery Cartridges
- o Services

Features:

- O Cascading capabilities
- O Hot Pluggable Operation
- O Intelligent battery management

Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Standard Warranty 2 years repair or replace

<u>Copyright</u> © American Power Conversion Corp., all rights reserved <u>About APCInvestorsJob SeekersPressFeedbackContactPrivacy Policy</u>